



#### DESDA5V3LQ

#### DUAL SURFACE MOUNT TVS ARRAY

## **Product Summary**

V <sub>BR(Min)</sub>	I <sub>PP(Max)</sub>	C <sub>T(Max)</sub>
5.3V	20A	220pF

#### Description

This new generation TVS is designed to protect sensitive electronics from the damage due to ESD. The combination of small size and high ESD surge capability makes it ideal for use in Automotive Infotainment applications.

- USB Modules
- HDMI Inputs
- Infotainment Consoles



SOT23


Top View

#### Features and benefits

- Provides ESD Protection per IEC 61000-4-2 Standard: Air – ±16kV, Contact – ±9kV
- 2 Channels of ESD Protection
- 250W Peak Pulse Power
- Typically Used at Computers, Printers and Communication Systems
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

## **Mechanical Data**

- Case: SOT23
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish Annealed over Alloy 42 Leadframe (Lead Free Plating). Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.0089 grams (Approximate)



Device Schematic

## Ordering Information (Note 5)

Part Number	Compliance	Marking	Reel Size(inches)	Tape Width(mm)	Quantity Per Reel	
DESDA5V3LQ-7 Automotive		RD1	7	8	3,000/Tape & Reel	
Notes: 1, No purposely added lead, Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.						

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.


2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/.

5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

## **Marking Information**



RD1 = Product Type Marking Code

YM = Date Code Marking

Y = Year (ex: E = 2017)

M = Month (ex: 9 = September)

Date Code Key												
Year	201	7	2018		2019	20	20	2021		2022	1	2023
Code	E		F		G	ł	4			J		K
Month	Jan	Feb	Mar	Apr	Мау	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



# **Maximum Ratings** (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	Conditions
Peak Pulse Power Dissipation	P <sub>PP</sub>	250	W	8/20µs, Figure 2
Peak Pulse Current	IPP	20	А	8/20µs, Figure 2
ESD Protection – Contact Discharge	V <sub>ESD_Contact</sub>	±9	kV	Standard IEC 61000-4-2
ESD Protection – Air Discharge	V <sub>ESD_Air</sub>	±16	kV	Standard IEC 61000-4-2
ESD Protection – Human Body Model	V <sub>HBM</sub>	±25	kV	MIL STD 883C – Method 3015-6

## **Thermal Characteristics**


Characteristic	Symbol	Value	Unit
Power Dissipation (Note 6)	PD	250	mW
Thermal Resistance, Junction to Ambient (Note 6)	R <sub>0JA</sub>	500	°C/W
Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>STG</sub>	-55 to +150	°C


# Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Conditions
Reverse Breakdown Voltage	V <sub>BR</sub>	5.3	—	5.9	V	I <sub>R</sub> = 1mA
Reverse Current (Note 7)	I <sub>RM</sub>	_	—	2	μA	$V_{RM} = 3V$
Forward Voltage	VF	—	—	1.25	V	I <sub>F</sub> = 200mA
Dynamic Resistance	R <sub>D</sub>	_	0.28	—	Ω	lpp = 15A, t <sub>P</sub> = 2.5µs
Channel Input Capacitance	C <sub>IN</sub>		_	220	pF	$V_{IN} = 0V, f = 1MHz$

Notes: 6. Device mounted on FR-4 PCB pad layout (2oz copper) as shown in Diodes Incorporated's package outline PDFs, which can be found on our website at http://www.diodes.com/package-outlines.html.

7. Short duration pulse test used to minimize self-heating effect.







# **DESDA5V3LQ**

 $T_A = 25^{\circ}C$ 


3


4


2

V<sub>R</sub>, INSTANTANEOUS REVERSE VOLTAGE (V)

Figure 6 Typical Reverse Characteristics







10

1


ō



# **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.


SOT23



	SOT23						
Dim	Min	Max	Тур				
Α	0.37	0.51	0.40				
В	1.20	1.40	1.30				
С	2.30	2.50	2.40				
D	0.89	1.03	0.915				
F	0.45	0.60	0.535				
G	1.78	2.05	1.83				
н	2.80	3.00	2.90				
J	0.013	0.10	0.05				
ĸ	0.890	1.00	0.975				
K1	0.903	1.10	1.025				
L	0.45	0.61	0.55				
L1	0.25	0.55	0.40				
М	0.085	0.150	0.110				
а	0°	8°					
All	All Dimensions in mm						

# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.



SOT23

Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
Y1	2.9



#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com