



DMP1022UFDF

### **Product Summary**

BV <sub>DSS</sub>	R <sub>DS(ON)</sub> max	I <sub>D</sub> max T <sub>A</sub> = +25°C
	14.8mΩ @ V <sub>GS</sub> = -4.5V	-9.5A
-12V	19mΩ @ V <sub>GS</sub> = -2.5V	-8.5A
-120	26mΩ @ V <sub>GS</sub> = -1.8V	-7.2A
	32mΩ @ V <sub>GS</sub> = -1.5V	-6.6A

## Description

This MOSFET is designed specifically for use in battery management applications.


#### Features

- 0.6mm Profile Ideal for Low Profile Applications
- PCB Footprint of 4mm<sup>2</sup>
- Low Gate Threshold Voltage
- Fast Switching Speed
- ESD Protected Gate
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/product-definitions/</u>

**12V P-CHANNEL ENHANCEMENT MODE MOSFET** 

# Mechanical Data

- Case: U-DFN2020-6
- Case Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish NiPdAu over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (e4)
- Weight: 0.0065 grams (Approximate)



## Ordering Information (Note 4)

Part Number	Case	Packaging
DMP1022UFDF-7	U-DFN2020-6 (Type F)	3,000/Tape & Reel
DMP1022UFDF-13	U-DFN2020-6 (Type F)	10,000/Tape & Reel

Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.

2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.


3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.



## **Marking Information**

Site 1



PU = Product Type Marking Code YM = Date Code Marking Y = Year (ex: H = 2020) M = Month (ex: 9 = September)

Date Code Key

Year	2013		2020	2021	2022	2023	2024	2025	2026	2027	2028	2029
Code	A		Н		J	К	L	М	Ν	0	Р	R
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec

Site 2



PU = Product Type Marking Code YWX = Date Code Marking Y = Year (ex: 0 = 2020) W = Week (ex: a = Week 27; z Represents Week 52 and 53) X = Internal Code (ex: U = Monday)

Date	Code	Kev
Date	Coue	1/0/

Year	2013		2020	2021	2022	2023	2024	2025	2026	2027	2028	2029
Code	3		0	1	2	3	4	5	6	7	8	9
Week		1-	26			27-	-52			5	3	
Code		A	-Z			a	-Z			Z	7	
Internal Code	Sun	1	Mon		Tue	W	ed	Thu		Fri		Sat
Code	Т		U		V	٧	V	Х		Y		Z



# Maximum Ratings (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Drain-Source Voltage		VDSS	-12	V	
Gate-Source Voltage			V <sub>GSS</sub>	±8	V
	Steady State	T <sub>A</sub> = +25°C T <sub>A</sub> = +70°C	ID	-9.5 -7.6	А
Continuous Drain Current (Note 6) V <sub>GS</sub> = -4.5V	t<5s	T <sub>A</sub> = +25°C T <sub>A</sub> = +70°C	lD	-11.0 -8.8	А
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%	)		I <sub>DM</sub>	-90	А
Continuous Source-Drain Diode Current	T <sub>A</sub> = +25°C T <sub>C</sub> = +25°C	ls	-2.5 -7.1	А	
Pulsed Source-Drain Diode Current (10µs Pulse, Du	lsм	-50	А		

## **Thermal Characteristics**

Characteristic		Symbol	Value	Unit	
Total Dower Dissinction (Note 5)	T <sub>A</sub> = +25°C	D	0.73	W	
Total Power Dissipation (Note 5)	$T_A = +70^{\circ}C$	PD	0.47		
Thermal Resistance, Junction to Ambient (Note 5)	Steady State	Devi	172	°C/W	
Thermal Resistance, Junction to Amblent (Note 5)	t<5s	R <sub>0JA</sub>	128	C/W	
Tatal Bawar Dissinction (Nata 6)	$T_A = +25^{\circ}C$	Π-	2.1	W	
Total Power Dissipation (Note 6)	$T_A = +70^{\circ}C$	PD	1.3		
Thermal Resistance, Junction to Ambient (Note 6)	Steady State	Devi	59		
mermai Resistance, Junction to Ambient (Note 6)	t<5s	Reja	45	°C/W	
Thermal Resistance, Junction to Case (Note 6)	Steady State	Rejc	5.1		
Operating and Storage Temperature Range		TJ, TSTG	-55 to +150	°C	

## Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 7)			71			
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	-12			V	$V_{GS} = 0V, I_D = -250\mu A$
Zero Gate Voltage Drain Current TJ = +25°C	IDSS	_	—	-200	nA	V <sub>DS</sub> = -12V, V <sub>GS</sub> = 0V
Zero Gate Voltage Drain Current TJ = +55°C (Note 8)	IDSS	_	—	-2	μA	V <sub>DS</sub> = -12V, V <sub>GS</sub> = 0V
Gate-Source Leakage	lgss	_	—	±10	μA	$V_{GS} = \pm 8V, V_{DS} = 0V$
ON CHARACTERISTICS (Note 7)						·
Gate Threshold Voltage	V <sub>GS(TH)</sub>	-0.35	—	-0.8	V	$V_{DS} = V_{GS}, I_D = -250 \mu A$
			12	14.8		VGS = -4.5V, ID = -4A
Static Drain-Source On-Resistance	<b>D</b>	—	15	19	mΩ	VGS = -2.5V, ID = -4A
Static Drain-Source Off-Resistance	R <sub>DS(ON)</sub>		20	26	11122	Vgs = -1.8V, ID = -4A
			23	32		VGS = -1.5V, ID = -2A
Diode Forward Voltage	V <sub>SD</sub>	_	-0.8	-1.2	V	$V_{GS} = 0V, I_{S} = -8A$
DYNAMIC CHARACTERISTICS (Note 8)						·
Input Capacitance	Ciss		2,712	—		
Output Capacitance	Coss		514	_	pF	$V_{DS} = -10V$ , $V_{GS} = 0V$ , f = 1.0MHz
Reverse Transfer Capacitance	Crss		467	—		
Gate Resistance	Rg		8.6	18	Ω	$V_{DS} = 0V, V_{GS} = 0V, f = 1MHz$
Total Gate Charge	Qg		48.3	—		VGS = -8V, VDS = -6V, ID = -10A
Total Gate Charge	Qg	_	28.6	—	nC	
Gate-Source Charge	Qgs	—	4.2	—	nc	$V_{GS} = -4.5V, V_{DS} = -6V,$ ID = -10A
Gate-Drain Charge	Qgd	—	7.0	—		ID = -IOA
Turn-On Delay Time	t <sub>D(ON)</sub>	_	25.1	_		
Turn-On Rise Time	tR		39.8	—	-	VDS = -6V, VGS = -4.5V,
Turn-Off Delay Time	tD(OFF)		141		ns	$R_G = 1\Omega$ , $I_D = -8A$
Turn-Off Fall Time	tF		147	—		

Notes: 5. Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided.

6. Device mounted on FR-4 substrate PC board, 2oz copper, with thermal vias to bottom layer 1inch square copper plate.

7. Short duration pulse test used to minimize self-heating effect.


8. Guaranteed by design. Not subject to production testing.



## DMP1022UFDF

3

20




150

125



## DMP1022UFDF



Datasheet number: DS36624 Rev. 6 - 2


5 of 7 www.diodes.com

January 2020 © Diodes Incorporated



### **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.




U-DFN2020-6							
	-	be F)					
Dim	Min	Max	Тур				
Α	0.57	0.63	0.60				
A1	0.00	0.05	0.03				
A3	-	-	0.15				
b	0.25	0.35	0.30				
D	1.95	2.05	2.00				
D2	0.85	1.05	0.95				
D2a	0.33	0.43	0.38				
Е	1.95	2.05	2.00				
E2	1.05	1.25	1.15				
E2a	0.65	0.75	0.70				
e	0.65 BSC						
e2	C	).863 BS	SC				
e3	(	0.70 BS	С				
e4	C	).325 BS	SC				
k	(	0.37 BS	С				
k1	(	0.15 BS	С				
k2	(	0.36 BS	С				
L	0.225	0.325	0.275				
z	(	0.20 BS	С				
z1	C	).110 BS	SC				
z2		0.20 BS	С				
All C	Dimens	ions in	mm				

# Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

#### U-DFN2020-6 (Type F)



Dimensions	Value (in mm)
С	0.650
Х	0.400
X1	0.480
X2	0.950
X3	1.700
Y	0.425
Y1	0.800
Y2	1.150
Y3	1.450
Y4	2.300

#### U-DFN2020-6 (Type F)



#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com