



DMP10H400SE

100V P-CHANNEL ENHANCEMENT MODE MOSFET

Product Summary

BV _{DSS}	R _{DS(ON)} Max	I _D T _A = +25°C	
-100V	250mΩ @ $V_{GS} = -10V$	-2.3A	
	300 m Ω @ V _{GS} = -4.5V	-2.1A	

Description

This MOSFET is designed to minimize the on-state resistance and yet maintain superior switching performance, making it ideal for high efficiency power management applications.

Applications

- Motor Control
- DC-DC Converters
- Power Management Functions
- Uninterrupted Power Supply

Features and Benefits

- Low Gate Drive
- Low Input Capacitance
- Fast Switching Speed
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- An Automotive-Compliant Part is Available Under Separate Datasheet (DMP10H400SEQ)


Mechanical Data

- Case: SOT223
- Case Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals Connections: See Diagram Below
- Terminals: Finish Matte Tin Annealed over Copper Lead Frame.
 Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.112 grams (Approximate)






Top View



Pin Out - Top View




Ordering Information (Note 4)

Part Number	Case	Packaging		
DMP10H400SE-13	SOT223	2,500 / Tape & Reel		

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- 2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

Marking Information



O!! = Manufacturer's Marking P400SE = Marking Code YWW = Date Code Marking Y or Y= Year (ex: 5 = 2015) WW = Week (01 to 53)



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Drain-Source Voltage	V_{DSS}	-100	V		
Gate-Source Voltage	V _{GSS}	±20	V		
Continuous Drain Current, V _{GS} = -10V (Note 5)	Steady State	$T_{C} = +25^{\circ}C$ $T_{A} = +25^{\circ}C$	I _D	-6.0 -2.3	А
Maximum Body Diode Forward Current (Note 5)	Is	-1.9	Α		
Pulsed Drain Current (380μs Pulse, Duty Cycle = 1%	I _{DM}	-10	Α		

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Total Power Dissipation (Note 5)	$T_A = +25^{\circ}C$	0	2.0	W
Total Power Dissipation (Note 5)	T _A = +70°C	P _D	1.3	
Thermal Resistance, Junction to Ambient (Note 5)	$R_{\theta JA}$	62	°C/W	
Total Power Dissipation (Note 5) $T_C = +25^{\circ}C$		P _D	13.7	W
Thermal Resistance, Junction to Case (Note 5)	R _{0JC}	9.1	°C/W	
Operating and Storage Temperature Range	T_{J} , T_{STG}	-55 to +150	°C	


Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 6)	Cymbol	.,,,,,,	1 7 7	IIIUX	Oint	Tool Containon	
Drain-Source Breakdown Voltage	BV _{DSS}	-100	_	_	V	$V_{GS} = 0V, I_{D} = -250\mu A$	
Zero Gate Voltage Drain Current	I _{DSS}	_	_	1	μA	$V_{DS} = -80V, V_{GS} = 0V$	
Gate-Source Leakage	I _{GSS}	_	_	±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 6)							
Gate Threshold Voltage	V _{GS(TH)}	-1.0	-2.2	-3.0	V	$V_{DS} = V_{GS}, I_{D} = -250 \mu A$	
Static Drain-Source On-Resistance		_	203	250	mΩ	$V_{GS} = -10V, I_{D} = -5A$	
Static Drain-Source On-Resistance	R _{DS(ON)}	_	241	300	1117.5	$V_{GS} = -4.5V, I_{D} = -5A$	
Diode Forward Voltage	V_{SD}	_	-0.9	-1.2	V	$V_{GS} = 0V, I_{S} = -5A$	
DYNAMIC CHARACTERISTICS (Note 7)							
Input Capacitance	C _{iss}	_	1239	_		V _{DS} = -25V, V _{GS} = 0V, f = 1.0MHz	
Output Capacitance	Coss	_	42	_	pF		
Reverse Transfer Capacitance	C _{rss}	_	28	_			
Gate Resistance	Rg	_	13	_	Ω	$V_{DS} = 0V, V_{GS} = 0V, f = 1.0MHz$	
Total Gate Charge (V _{GS} = -4.5V)	Qg	_	8.4	_			
Total Gate Charge (V _{GS} = -10V)	Qg	_	17.5	_	nC	$V_{DS} = -60V, I_D = -5A$	
Gate-Source Charge	Q_{gs}	_	2.8	_	nc nc		
Gate-Drain Charge	Q_{gd}	_	3.2	_			
Turn-On Delay Time	t _{D(ON)}	_	9.1	_		$V_{DD} = -50V$, $R_G = 9.1\Omega$, $I_D = -5A$	
Turn-On Rise Time	t _R	_	14.9	_			
Turn-Off Delay Time	t _{D(OFF)}	_	57.4	_	ns		
Turn-Off Fall Time	t _F	_	34.4	_			
Body Diode Reverse Recovery Time	t _{RR}	_	25.2	_	ns	$V_{GS} = 0V$, $I_S = -5A$, $di/dt = 100A/\mu s$	
Body Diode Reverse Recovery Charge	Q _{RR}	_	24.5	_	nC	$V_{GS} = 0V$, $I_{S} = -5A$, $di/dt = 100A/\mu s$	

Notes:


- 5. Device mounted on FR-4 substrate PC board, 2oz copper, with 1inch square copper plate.6. Short duration pulse test used to minimize self-heating effect.7. Guaranteed by design. Not subject to production testing.









and Gate Voltage



Junction Temperature










Figure 6. On-Resistance Variation with Junction
Temperature

DMP10H400SE












Figure 9. Diode Forward Voltage vs. Current















Figure 13. Transient Thermal Resistance



Package Outline Dimensions

Please see AP02002 at http://www.diodes.com/datasheets/ap02002.pdf for the latest version.

SOT223




SOT223					
Dim	Min	Max	Тур		
Α	1.55	1.65	1.60		
A1	0.010	0.15	0.05		
b	0.60	0.80	0.70		
b1	2.90	3.10	3.00		
C	0.20	0.30	0.25		
D	6.45	6.55	6.50		
Е	3.45	3.55	3.50		
E1	6.90	7.10	7.00		
е	-	-	4.60		
e1	-	-	2.30		
١	0.85	1.05	0.95		
Q	0.84	0.94	0.89		
All Dimensions in mm					

Suggested Pad Layout

Please see AP02001 at http://www.diodes.com/datasheets/ap02001.pdf for the latest version.

SOT223



Dimensions	Value (in mm)
С	2.30
C1	6.40
Х	1.20
X1	3.30
Y	1.60
Y1	1.60
Y2	8.00



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2015, Diodes Incorporated

www.diodes.com