

DMTH12H007SPSWQ 120V 175°C N-CHANNEL ENHANCEMENT MODE MOSFET

PowerDI5060-8

ΠD

ΠD

ΠD

Πр

Product Summary

BV _{DSS}	Rds(on) Max	I _D Tc = +25°C (Note 10)
120V	$8.9 \text{m}\Omega @ V_{GS} = 10 \text{V}$	84A
	$16m\Omega @ V_{GS} = 6V$	70A

Description and Applications

This MOSFET is designed to minimize the on-state resistance (RDS(ON)) yet maintain superior switching performance, making it ideal for high efficiency power management applications.

- Switching
- DC-DC converters


Features and Benefits

- Rated to +175°C Ideal for High Ambient Temperature Environments
- 100% Unclamped Inductive Switching (UIS) Test in Production Ensures More Reliable and Robust End Application
- Thermally Efficient Package Cooler Running Applications
- High Conversion Efficiency
- Low RDS(ON) Minimizes On-State Losses
- <1.1mm Package Profile Ideal for Thin Applications
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The DIODES™ DMTH12H007SPSWQ is suitable for automotive applications requiring specific change control; this part is AEC-Q101 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/

Mechanical Data

- Package: PowerDI[®]5060-8
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Finish Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 (3)
- Weight: 0.097 grams (Approximate)



Ordering Information (Note 4)

Part Number	Paakaga	Packing		
Fait Nulliper	Package	Qty.	Carrier	
DMTH12H007SPSWQ-13	PowerDI5060-8 (SWP) (Type UX)	2,500	Tape & Reel	


Notes: 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied. 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and

Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



PowerDI is a registered trademark of Diodes Incorporated.



Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage	VDSS	120	V	
Gate-Source Voltage	V _{GSS}	±20	V	
Continuous Drain Current, V _{GS} = 10V (Note 6)	Tc = +25°C (Note 10) Tc = +100°C	ID	84 60	A
Pulsed Drain Current (10µs Pulse, T _C = +25°C, Package Limited)		Ідм	336	А
Continuous Body Diode Forward Current (Note 6) T _C = +25°C		ls	84	А
Pulsed Body Diode Current (10µs Pulse, T _C = +25°C, Package Limited)	lsм	336	А	
Avalanche Current, L = 3mH (Note 9)	I _{AS}	15.5	А	
Avalanche Energy, L = 3mH (Note 9)		Eas	360.4	mJ

Thermal Characteristics

Characteristic	Symbol	Value (Typ.)	Unit
Total Power Dissipation (Note 5)	PD	3.5	W
Thermal Resistance, Junction to Ambient (Note 5)	Reja	43	°C/W
Total Power Dissipation (Note 6)	PD	125	W
Thermal Resistance, Junction to Case (Note 6)	Rejc	1.2	°C/W
Operating and Storage Temperature Range	TJ, TSTG	-55 to +175	°C


Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 7)	CjDCi				•		
Drain-Source Breakdown Voltage	BVDSS	120	_		V	$V_{GS} = 0V$, $I_D = 10mA$	
Zero Gate Voltage Drain Current	IDSS		—	1	μA	VDS = 96V, VGS = 0V	
Gate-Source Leakage	IGSS	_	_	±100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$	
ON CHARACTERISTICS (Note 7)							
Gate Threshold Voltage	VGS(TH)	2	_	4	V	$V_{DS} = V_{GS}$, $I_D = 250 \mu A$	
Static Drain-Source On-Resistance		—	7.5	8.9	mΩ	$V_{GS} = 10V, I_{D} = 30A$	
Static Drain-Source On-Resistance	RDS(ON)	_	12	16	1112	Vgs = 6V, ID = 10A	
Diode Forward Voltage	V _{SD}	_	0.8	1.2	V	$V_{GS} = 0V, I_{S} = 30A$	
DYNAMIC CHARACTERISTICS (Note 8)							
Input Capacitance	Ciss	—	3142	—		$V_{DS} = 60V, V_{GS} = 0V,$ f = 1MHz	
Output Capacitance	Coss	_	665	_	pF		
Reverse Transfer Capacitance	Crss	_	29	_			
Gate Resistance	R _G		1.9		Ω	$V_{DS} = 0V, V_{GS} = 0V, f = 1MHz$	
Total Gate Charge (V _{GS} = 10V)	Qg	_	44			V _{DS} = 60V, I _D = 25A	
Gate-Source Charge	Qgs		15		nC		
Gate-Drain Charge	Qgd	_	9				
Turn-On Delay Time	tD(ON)	_	12.5			V _{DD} = 60V, V _{GS} = 10V,	
Turn-On Rise Time	t _R		13.7				
Turn-Off Delay Time	tD(OFF)	_	24.4	_	ns	$I_D = 25A, R_G = 2.7\Omega$	
Turn-Off Fall Time	tF	_	10.9	_	1		
Reverse Recovery Time	trr	_	55	_	ns		
Reverse Recovery Charge	Qrr	—	105	_	nC	IF = 25A, di/dt = 100A/μs	

 Device mounted on FR-4 substrate PC board, 2oz copper, with thermal bias to bottom layer 1inch square copper plate.
Thermal resistance from junction to soldering point (on the exposed drain pad).
Short duration pulse test used to minimize self-heating effect.
Guaranteed by design. Not subject to product testing. Notes:

9. I_{AS} and E_{AS} ratings are based on low frequency and duty cycles to keep $T_J = +25^{\circ}C$. 10. Package limited.












DMTH12H007SPSWQ












Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




PowerDI5060-8 (SWP) (Type UX)

PowerDI5060-8 (SWP)					
(Type UX)					
Dim	Min	Max	Тур		
Α	0.90	1.10	1.00		
A1	0	0.05			
b	0.30	0.50	0.41		
b2	0.20	0.35	0.25		
b4	().25REF			
С	0.230	0.330	0.277		
D	-	.15 BS0	-		
D1	4.70	5.10	4.90		
D2	3.56	3.96	3.76		
D2a	3.78	4.18	3.98		
Е	6	.40 BS0	0		
E1	5.60	6.00	5.80		
E2	3.46	3.86	3.66		
E2a	4.195	4.595	4.395		
е	1	.27BSC	;		
k	1.05				
L	0.635	0.835	0.735		
La	0.635	0.835	0.735		
L1	0.200	0.400	0.300		
L1a	0.050REF				
L4	0.025	0.225	0.125		
М	3.205	4.005	3.605		
θ	10°	12°	11°		
θ1	6°	8°	7°		
All	All Dimensions in mm				

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.



PowerDI5060-8 (SWP) (Type UX)

Dimensions	Value		
Dimensions	(in mm)		
С	1.270		
G	0.660		
G1	0.820		
Х	0.610 4.100		
X1			
X2	4.420		
Y	1.270		
Y1	1.020		
Y2	3.810		
Y3	6.610		



IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

and 5 Diodes' products provided subject to Diodes' Standard Terms Conditions of Sale are (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

DIODES is a trademark of Diodes Incorporated in the United States and other countries. The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. © 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com