



#### DMWSH120H28SM4

# 1200V N-CHANNEL SILICON CARBIDE POWER MOSFET

### **Product Summary**

BV <sub>DSS</sub>	R <sub>DS(ON)</sub> Max	I <sub>D</sub> T <sub>C</sub> = +25°C
1200V	28.5mΩ @V <sub>GS</sub> = 15V	100A

## **Description and Applications**

This SiC MOSFET is designed to minimize the on-state resistance yet maintain superior switching performance, making it ideal for high-efficiency power-management applications.

- EV high-power DC-DC converters
- EV charging systems
- AC-DC traction inverters
- Automotive motor drivers


# **Features and Benefits**

- Low On-Resistance
- High BV<sub>DSS</sub> Rating for Power Application
- Low Input Capacitance
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- An automotive-compliant part is available under separate datasheet (<u>DMWSH120H28SM4Q</u>)


### **Mechanical Data**

- Package: TO247-4
- Package Material: Molded Plastic, "Green" Molding Compound.
   UL Flammability Classification Rating 94V-0
- Terminal Connections: See Diagram
- Terminals: Finish Matte Tin Annealed over Copper Leadframe.
   Solderable per MIL-STD-202, Method 208 (3)
- Weight: 6.6 grams (Approximate)

#### TO247-4 Standard







Internal Schematic


#### **Ordering Information** (Note 4)

Part Number	Package	Packing			
Part Number	Fackage	Qty.	Carrier		
DMWSH120H28SM4	TO247-4 Standard	30 Pieces	Tube		

Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- $4. For packaging details, go to our website at \ https://www.diodes.com/design/support/packaging/diodes-packaging/. \\$

# **Marking Information**



D | | = Manufacturer's Marking 120H28SM4 = Product Type Marking Code YYWW or YYWW = Date Code Marking YY or YY = Last Two Digits of Year (ex: 24 = 2024) WW or WW = Week Code (01 to 53)



### **Maximum Ratings** (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit	
Drain-Source Voltage		V <sub>DSS</sub>	1200	V
Gate-Source Voltage (Dynamic)		Vgss	+19/-8	V
Gate-Source Voltage (Static)		Vgss	+15/-4	V
Continuous Drain Current (Notes 5, 9)	$T_C = +25$ °C $T_C = +100$ °C	I <sub>D</sub>	100 70.8	А
Continuous Diode Forward Current (Note 5)	Is	87	А	
Pulsed Source Current (10µs Pulse, Duty Cycle = 1%) (Note 5)	Isм	430	А	
Pulsed Drain Current (10µs Pulse, Duty Cycle = 1%) (Note 5)		I <sub>DM</sub>	430	Α

### Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit		
Total Power Dissipation (Note 5)	Tc = +25°C	Do	429	W	
Total Fower Dissipation (Note 3)	Tc = +100°C	PD	214	VV	
Thermal Resistance, Junction to Ambient (Note 6)	R <sub>θJA</sub>	28.8	°C/W		
Thermal Resistance, Junction to Case (Note 5)	Rejc	0.35	C/VV		
Operating and Storage Temperature Range		TJ, TSTG	-55 to +175	°C	


# **Electrical Characteristics** (@ $T_A = +25$ °C, unless otherwise specified.)

Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition	
OFF CHARACTERISTICS (Note 8)							
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	1200	_	_	V	V <sub>G</sub> S = 0, I <sub>D</sub> = 100μA	
Zero Gate Voltage Drain Current	IDSS	_		50	μA	V <sub>DS</sub> = 1200V, V <sub>GS</sub> = 0	
Gate-Source Leakage	I <sub>GSS</sub>	_		±250	nA	$V_{GS} = +15/-4V, V_{DS} = 0$	
ON CHARACTERISTICS (Note 8)							
Gate Threshold Voltage	Vgs(TH)	1.8	2.5	3.6	V	$V_{DS} = V_{GS}$ , $I_D = 17.7$ mA	
Static Drain-Source On-Resistance	RDS(ON)	1	20	28.5	mΩ	$V_{GS} = 15V, I_{D} = 50A$	
Diode Forward Voltage	$V_{SD}$	1	3.8	1	V	$V_{GS} = -4V, I_{S} = 25A$	
Transconductance	gfs	1	15	1	S	$V_{DS} = 20V, I_{D} = 50A$	
DYNAMIC CHARACTERISTICS (Note 7)							
Input Capacitance	Ciss	1	3944	_			
Output Capacitance	Coss	_	180	_	pF	$V_{GS} = 0$ , $V_{DS} = 1000V$ , $V_{AC} = 25mV$ , $f = 1MHz$	
Reverse Transfer Capacitance	C <sub>rss</sub>	_	9.73	_			
Coss Stored Energy	Eoss	1	114.6	-	μJ		
Turn-On Switching Energy (Body Diode Forward)	Eon		744		μJ	$V_{GS} = -4V/+15V$ , $V_{DS} = 800V$ , $Rg = 5\Omega$ , $I_{D} = 50A$ , $L = 157\mu H$	
Turn-Off Switching Energy (Body Diode Forward)	Eoff	1	367				
Gate Resistance	$R_g$	1	1.3	1	Ω	$V_{AC} = 25mV, f = 1MHz$	
Total Gate Charge	Qg	1	173.7	1		Vgs = -4V/+15V, Vps = 800V, ID = 50A	
Gate-Source Charge	Qgs	_	51.9	_	nC		
Gate-Drain Charge	$Q_{gd}$	_	56.4	_			
Turn-On Delay Time	td(ON)	_	23.83	_		$V_{GS}$ = -4V/+15V, $V_{DD}$ = 800V, $Rg$ = 5 $\Omega$ , Inductive Load	
Turn-On Rise Time	t <sub>R</sub>	_	40.06	_	ns		
Turn-Off Delay Time	tD(OFF)	_	48.00	_	115		
Turn-Off Fall Time	tF	_	12.52	_			
Body Diode Reverse-Recovery Time	t <sub>RR</sub>	_	23.13	_	ns	V <sub>GS</sub> = -4V, V <sub>DS</sub> = 800V, -1 <sub>D</sub> = 50A, di/dt = 2600A/μs	
Body Diode Reverse-Recovery Charge	Q <sub>RR</sub>	_	423.9	_	nC		
Body Diode Reverse-Recovery Current	IRRM		30.12	_	Α		

- 5. Device mounted on an infinite heatsink.
- 6. Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.
- 7. Guaranteed by design. Not subject to production testing.
- 8. Short duration pulse test used to minimize self-heating effect.
- 9. Drain current limited by maximum junction temperature.










Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage





Figure 5. Typical On-Resistance vs. Drain Current and Temperature






Figure 4. Typical Transfer Characteristic




Figure 6. On-Resistance Variation with Temperature









Figure 7. On-Resistance Variation with Temperature



20
15  $V_{DS} = 800V, I_{D} = 50A$   $V_{DS} = 800V, I_{D} = 50A$ 

Figure 11. Gate Charge




Figure 8. Gate Threshold Variation vs. Junction Temperature




Figure 10. Typical Junction Capacitance




Figure 12. SOA, Safe Operation Area







Figure 13. Transient Thermal Resistance




# **Package Outline Dimensions**


Please see http://www.diodes.com/package-outlines.html for the latest version.

#### TO247-4 Standard



TO247-4 Standard				
Dim	Min	Max		
Α	4.83	5.21		
A1	2.29	2.54		
A2	1.91	2.16		
b	1.07	1.33		
b1	2.39	2.94		
b3	1.07	1.60		
b5	2.39	2.69		
С	0.55	0.68		
D	23.30	23.60		
D1	16.25	17.65		
D2	0.95	1.25		
E	15.75	16.30		
E1	13.10	14.15		
E2	3.68	5.10		
E3	1.00	1.90		
E4	12.38	13.43		
е	2.54 BSC			
e1	5.08 BSC			
L	17.31	17.82		
L1	3.97	4.37		
L2	2.35	2.65		
ØP	3.51	3.65		
Q	5.49	6.00		
S	6.04	6.30		
θ	17.5°- 20° REF			
θ1	3.5°- 5° REF			
θ2	4°- 5° REF			
All Dimensions in mm				







#### **IMPORTANT NOTICE**

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- provided subject Diodes' products are tο Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2024 Diodes Incorporated. All Rights Reserved.

www.diodes.com