

THROUGH-HOLE PACKAGING REELS, TUBES, AMMO PACKS & TAPING SPECIFICATIONS

MINIMUM PACKAGING QUANTITY

		MINIMUM PACKAGIN				
	Available Packaging					
Device Type		Bulk		13"Ø Tape & Reel	Ammo Pack	
Device Type	Quantity per Box	Quantity per Tube	Quantity per Tray	Quantity per Reel	Quantity per Box	
5KP	500			500 / 700*		
5W	1K			3K		
5KW				1K		
A-405	1K			5K	3K	
DF-M	5K	50				
DO-15	500 / 800 / 1K*			4K	2K	
D0-201	1K			1K / 1.2K*	1K	
DO-201AD	500/ 1K			1.2K	1K	
DO-35	500			10K	5K / 10K*	
DO-41	500 / 1K*			5K	3K / 5K*	
E-LINE	4K				2K	
GBJ	750	15				
GBPC/W			100			
GBU	1K	20				
KBJ	1K	20				
KBP	3.5K	35				
KBPC/W			100			
MB/W			100			
MP/W			100			
PBL			100			
PBPC-3			200			
PBPC-8	150					
PBU			100			
R-6	200 / 500*			500 / 700*		
T-1	1K			5K	3K	
TO126	4K					
TO220AB/AC, ITO-220AB,	1K / 2K*	50				
ITO-220S, TO262						
TO220F	1K	50				
TO-247 (Type WH)		30				
TO251	3K	75				
TO3P	1.2K	30				
TO92	2K / 5K /10K*				2K / 4K*	
TO92L					2K	
WOG	1K					

^{*} Quantity varies by Part Number.

1. Package quantities are given for minimum packaging quantity only, not minimum order quantity. For minimum order quantity, please Notes: consult the Sales Department.

 $^{2. \} No \ mixed \ date \ codes \ or \ partial \ quantity \ (less \ than \ minimum \ packaging \ quantity) \ per \ packaging \ is \ allowed.$

^{3.} In no case shall there be two or more consecutive components missing from any real for any reason.





PRODUCT REEL DIMENSIONS

PRODUCT REEL						
Description			ication	Alternate		
Description	Symbol	Inches	Millimeters	Inches	Millimeters	
Arbor Hole Diameter	D_0	0.65 ± 0.02	16.6 ± 0.50	1.18 ± 0.02	30.0 ± 0.50	
Core Diameter (O.D)	D ₁	3.2 Typical	81.0 Typical	3.2 Typical	81.0 Typical	
Reel Diameter	D ₂	13.6 ± 0.6	345.0 ± 15.0	10.25 ± 0.6	260.0 ± 15.0	
Drive Hole Diameter	D ₃	0.38 ± 0.02	9.5 ± 0.5	0.38 ± 0.02	9.5 ± 0.5	
Material Thickness	W ₀	0.08 - 0.16	2.0 – 4.0	0.08 - 0.16	2.0 – 4.0	
Reel Width	W ₁	3.15 ± 0.20	80.0 ± 5.0	2.56 ± 0.20	65.0 ± 5.0	
Drive/ Arbor Hole Spacing	W ₂	1.08 ± 0.02	27.5 ± 0.5	1.08 ± 0.02	27.5 ± 0.5	


Core material: plastic (blue/black) or metal (neutral) Reel material: corrugated board or plastic (blue or black)

For label dimensions and placement see AP02006.





Direction of Unreeling






REEL/ AMMO PACK TAPING SPECIFICATIONS

REEL AND AMMO PACK TAPING SPECIFICATIONS						
Description	Symbol	Body	Specification (mm)			
0	۸	DO-15, DO-35, DO-41, A-405, 5W	5.0 ± 0.5			
Component Pitch	A	DO-201, DO-201AD, 5KP, 5KW, R-6	10.0 ± 0.5			
Inside Tape Spacing	В	All	52.4 ± 1.5			
Lead to Lead Eccentricity	D ₁ - D ₂	All	1.4 max			
Lead Extension	K	All	0.8 max			
Lead Bending	M	All	1.2 max			
Cumulative Pitch	Р	All	±1.5 per 6 pitch			
Exposed Adhesive	S	All	0.8 max			
Tape Width	Т	All	6.0 ± 0.4			
Empty Spaces			< 0.1%			
	All polarized components shall be oriented in the same direction.					
Polarity Marking	The cathode tape shall be colored, and the anode tape shall be white or light beige.					
	Anode end must face label-side of reel. See AP02006 for label placement.					

Notes: 1. Consecutive missing components not allowed.






TUBE PACK DIMENSIONS/ SPECIFICATIONS

TUBE PACK							
PRODUCT DESCRIPTION	Heig	ht (H)	Widt	h (W)	Leng	jth (L)	Drawing
PRODUCT DESCRIPTION	inches	mm	inches	mm	inches	mm	Reference
DF-M	0.6	15	0.5	13.3	17.5	444	
GBJ	1.7	42.5	0.3	7.2	18.7	475	
GBU	1.6	41.5	0.2	6.2	18.3	465	Fig.1
ITO-220AB	1.3	33	0.27	6.8	20.83	529	Fig.2
110-220AB	1.26	32.09	0.26	6.75	21.02	534	Fig.3
ITO-220S	1.3	33	0.3	7	20.79	528	
KBJ	1.5	37.3	0.3	7.1	20.7	525	
КВР	1.2	29.6	0.2	6.2	20.9	531	
TO220AB	1.3	33	0.27	6.8	20.83	529	Fig.2
TOZZUAB	1.26	32.09	0.26	6.75	21.02	534	Fig.3
TO220AC	1.3	33	0.3	7	20.79	528	
TO220-5	1.3	33	0.27	6.8	20.83	529	Fig.2
10220-3	1.26	32.09	0.26	6.75	21.02	534	Fig.3
TO3P, TO247	1.8	46	0.3	8	19.8	502	
TO247 (Type WH)	1.8	46	0.3	7.7	21.0	533.5	Fig 4
TO262	1.3	33	0.3	7	20.79	528	


Fig.1



Dimension	Specification (mm)	Dimension	Specification (mm)	Dimension	Specification (mm)
D	2.45 ±0.1	H2	20.00±0.3	N	14.9 ±0.3
E	0.90 ±0.3	Н3	5.10 ±0.3	Р	2.90 ±0.1
F	2.05 +0.3/-0.1	H4	6.50±0.3	Т	0.80 ±0.3
Н	41.5±0.3	L	465+1/-0	W	6.20±0.2
H1	20.68±0.3	M	6.55±0.2		




Fig.2



Dimension	Specification (mm)	Dimension	Specification (mm)
H1	17.00 <u>+</u> 0.3	W1	5.60 <u>+</u> 0.3
H2	31.80 <u>+</u> 0.5	W2	4.60 <u>+</u> 0.3
H3	17.00 <u>+</u> 0.3	W3	3.00 <u>+</u> 0.3
H4	9.20 <u>+</u> 0.3	T	0.60+0.2/-0.05
L	529.0 <u>+</u> 01.0		


Fig.3



Dimension	Specification (mm)	Dimension	Specification (mm)
Н	32.09 <u>+</u> 0.10	L	534.0 <u>+</u> 01.0
H1	17.00 <u>+</u> 0.3	W	6.75 <u>+</u> 0.25
H2	17.50 <u>+</u> 0.5	Т	0.60 <u>+</u> 0.1
Н3	10.00 <u>+</u> 0.5		



Fig.4



PRINT Position: Left-Right center

Tolerance: +/- 3

ANTISTATIC STATIC SENSITIVE DEVICES HANDLE ONLY AT STATIC FREE STATION & PVC-X0121 2.5 +/-0.3 3.5 +/-0.3

Dimension	Specification (mm)	Dimension	Specification (mm)
Н	46	W1	2.2
H1	24.7	W2	1.5
L	533.5 <u>+</u> 01.0	Т	0.75
W	7.7		




AMMO PACK DIMENSIONS/ SPECIFICATIONS

AMMO PACK							
PRODUCT DESCRIPTION	Heig	ht (H)	Width (W) Leng		jth (L)		
	inches	mm	inches	mm	inches	mm	
DO-35, DO-41 Glass Case	4.88	124	3.00	75	10.00	255	
DO-41 Plastic Case	5.75	145	3.12	19	10.25	260	
E-LINE	5.90	150	1.57	40	8.66	220	
TO92	7.68	195	1.57	40	13.00	330	


Material: corrugated board (neutral) Thickness: 3.00 ± 0.5 mm (0.12 ± 0.02 ")

For label dimensions and placement see AP02006.






E-LINE TAPE AND AMMO PACKING



AMMO PACKING


Part No. suffixed STZ = 2,000 devices per box

Note: For MOS Pinout, substitute C=D, B=G and E=S





E-LINE AMMO TAPING SPECIFICATIONS




e,	/MBOL	ITEM DESCRIPTION	VALUE (mm)	
STWIBOL		HEW DESCRIPTION	Minimum	Maximum
1	ØDo	Sprocket hole not excessively burred	3.8	4.2
2	Po	Pitch of sprocket hole	12.4	13.0
3	P ₂	Distance between centre of sprocket hole and the middle lead of the following device.	5.95	6.75
4	F ₁ , F ₂	Lead spacing of devices Note: F ₁ & F ₂ are to be measured from the top of the carrier tape	2.44	2.94
5	Н	Distance between centre of sprocket hole and base of device body	18.0	20.0
6	Δh, Δh,	Maximum deviation of the body vertical to the tape plane from the nominal position.	-2.0	2.0
7	∆р, ∆р	Maximum deviation of the device body in the tape plane from the nominal position	-1.0	1.0
8	Но	Distance between centre of sprocket hole to the reference plane of joggled devices	15.5	16.5
9	W ₁	Distance from centre of sprocket hole to top of carrier tape.	8.5	9.5
10	U	Distance allowed below top of carrier tape by sealing tape.	0	0.5




TO92 TRANSISTOR - AMMO PACK

- Notes: 1. The carrier tape consists of a cardboard strip with sprocket holes. The pins of the transistors are secured radially to the carrier tape with a heat-seal tape.
 - 2. The tape can be taken from either of two opposite corners, depending on the desired pin sequence.
 - 3. The label shall contain a minimum of: Part Number, Type Designation, Quantity and Date Code.
 - 4. Each Ammo Pack consists of layers of 25 devices each, folded like a concertina. One component is missing at the end of each layer. Each such position is identified by means of a double perforation across the tape. The tape is folded at the perforations.
 - 5. See AP02006 for Label Dimensions and placement.



Position of the components when being withdrawn.




Position of the components when being withdrawn from opposite corner.




TO92 TAPING SPECIFICATIONS

THROUGH-HOLE TO-92 TAPING SPECIFICATIONS				
Description	Symbol	Specification (mm)		
Front to Rear Deflection	DA	0 ± 1.0		
Left to Right Deflection	DB	0 ± 1.0		
Feed Hole Diameter	D	4.0 ± 0.2		
Component Lead Pitch	F1, F2	2.5 +0.4 - 0.1		
Feed Hole to Bottom of Component	Н	21.0 max		
Height of Seating Plane	H1	16 ± 0.5		
Height of Feed Hole Location	H2	9.0 + 0.5		
Feed Hole Pitch	Р	12.7 ± 0.3		
Center of Seating Plane Location	P1	6.35 ± 0.5		
Total Taped Package Thickness	Т	1.5 max		
Carrier Tape Width	W	18.0 +1.0 - 0.5		
Adhesive Tape Width	W1	6.0 ± 0.5		
Adhesive Tape Position	W2	1.0 max		
Feed Hole Pitch Tolerance	_	0 ± 1.0 over 20 pitch		
Empty Places in Tape	<u> </u>	0.1%, non-consecutive		





TO92L AMMO TAPING SPECIFICATION



TO92L AMMO TAPING SPECIFICATIONS						
SYMBOL	ITEM DESCRIPTION	ITEM DESCRIPTION				
STWIBOL	TIEW DESCRIPTION	MIN	MAX	TYP		
ØDo	Sprocket hole not excessively burred	3.85	4.15	4.00		
Po	Pitch of sprocket hole	12.60	12.80	12.70		
P ₂	Distance between centre of sprocket hole and the centre of the middle lead of the adjacent device.	6.15	6.55	6.35		
P ₃	Distance between centre of sprocket hole and the centre of the nearest lead of the adjacent device.	3.65	4.05	3.85		
F ₁ , F ₂	Lead spacing of devices	2.30	2.70	2.50		
Н	Distance between centre of sprocket hole and base of device body	19.00	20.00	19.00		
Но	Distance between centre of sprocket hole to the reference plane of joggled devices	15.70	16.30	16.00		
H₁	Distance from the tip of the joggled leads to top of carrier tape	3.30	3.50	3.40		
Δh	Maximum deviation of the body vertical to the tape plane from the nominal position.	-1.00	+1.00	0		
Δр	Maximum deviation of the device body in the tape plane from the nominal position	-1.00	1.00	0		
W	Width of tape	17.50	19.00	18.00		
W ₁	Distance from centre of sprocket hole to top of carrier tape.	8.70	9.30	9.00		
W ₂	Distance from top of carrier tape to bottom of sealing tape.	5.70	6.30	6.00		
U	Distance allowed below top of carrier tape by sealing tape.	-	1.0	-		