

Product Summary


BV_{DSS}	$R_{DS(ON) Max}$	I_D $T_C = +25^\circ C$
1200V	80.5mΩ @ $V_{GS} = 18V$	44.5

Description and Applications

This SiC MOSFET is designed to minimize the on-state resistance yet maintain superior switching performance, making it ideal for high-efficiency power-management applications.

- SMPS (switching mode power supplies)
- UPS (uninterruptable power supplies)
- Energy storages
- EV charging systems
- Solar inverters

TO247 Standard




Pin Configuration

Features and Benefits

- Low On-Resistance
- High BV_{DSS} Rating for Power Application
- Low Input Capacitance
- **Lead-Free Finish; RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](mailto:contact@diodes.com) or your local Diodes representative. <https://www.diodes.com/quality/product-definitions/>**

Mechanical Data

- Package: TO247
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Terminal Connections: See Diagram
- Terminals: Finish – Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 **e3**
- Weight: 6.6 grams (Approximate)



Internal Schematic


Ordering Information (Note 4)

Part Number	Package	Packing	
		Qty.	Carrier
DMWSH120H80SM3	TO247 Standard	30 Pieces	Tube

- Notes:
1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
 2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
 4. For packaging details, go to our website at <https://www.diodes.com/design/support/packaging/diodes-packaging/>.

Marking Information

TO247 Standard



= Manufacturer's Marking
 120H80SM3 = Product Type Marking Code
 YYWW or YYWW = Date Code Marking
 YY or YY = Last Two Digits of Year (ex: 24 = 2024)
 WW or WW = Week Code (01 to 53)

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Drain-Source Voltage	V _{DSS}	1200	V
Gate-Source Voltage	V _{GS}	-10/+22	V
Gate-Source Voltage (Recommended Operating Values)	V _{GS}	-4/+18	V
Gate-Source Transient Voltage, t _p < 1μs, t ≤ 10 hours over Lifetime	V _{GS}	-11/+25	V
Continuous Drain Current (Notes 5, 9)	I _D	T _C = +25°C	44.5
		T _C = +100°C	31.4
Continuous Diode Forward Current (Note 5)	I _S	34	A
Pulsed Source Current (Pulse Width t _P Limited by T _{J Max}) (Note 5)	I _{SM}	80	A
Pulsed Drain Current (Pulse Width t _P Limited by T _{J Max}) (Note 5)	I _{DM}	80	A

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Total Power Dissipation (Note 5)	P _D	T _C = +25°C	238
		T _C = +100°C	119
Thermal Resistance, Junction to Ambient (Note 6)	R _{θJA}	28	°C/W
Thermal Resistance, Junction to Case (Note 5)	R _{θJC}	0.63	
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +175	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 8)						
Drain-Source Breakdown Voltage	BV _{DSS}	1200	—	—	V	V _{GS} = 0, I _D = 100μA
Zero Gate Voltage Drain Current	I _{DSS}	—	—	50	μA	V _{DS} = 1200V, V _{GS} = 0
Gate-Source Leakage	I _{GSS}	—	—	±200	nA	V _{GS} = +18/-4V, V _{DS} = 0
ON CHARACTERISTICS (Note 8)						
Gate Threshold Voltage	V _{GS(TH)}	1.7	2.5	3.5	V	V _{DS} = V _{GS} , I _D = 5mA
Static Drain-Source On-Resistance	R _{DS(ON)}	—	62	80.5	mΩ	V _{GS} = 18V, I _D = 20A
		—	75	—	mΩ	V _{GS} = 15V, I _D = 20A
Diode Forward Voltage	V _{SD}	—	4.5	—	V	V _{GS} = -4V, I _S = 10A
Transconductance	g _{fs}	—	4.2	—	S	V _{DS} = 20V, I _D = 20A
DYNAMIC CHARACTERISTICS (Note 7)						
Input Capacitance	C _{iss}	—	1069	—	pF	V _{GS} = 0, V _{DS} = 1000V, V _{AC} = 25mV, f = 1MHz
Output Capacitance	C _{oss}	—	56	—		
Reverse Transfer Capacitance	C _{rss}	—	4.17	—		
C _{oss} Stored Energy	E _{oss}	—	34.3	—	μJ	
Turn-On Switching Energy (Body Diode Forward)	E _{ON}	—	105	—	μJ	V _{GS} = -4V/+18V, V _{DS} = 800V, R _g = 5Ω, I _D = 20A, L = 156μH
Turn-Off Switching Energy (Body Diode Forward)	E _{OFF}	—	68	—		
Gate Resistance	R _g	—	2.7	—	Ω	V _{AC} = 100mV, f = 1MHz
Total Gate Charge	Q _g	—	59.1	—	nC	V _{GS} = -4V/+18V, V _{DS} = 800V, I _D = 20A
Gate-Source Charge	Q _{gs}	—	16.6	—		
Gate-Drain Charge	Q _{gd}	—	20.0	—		
Turn-On Delay Time	t _{d(ON)}	—	8.1	—	ns	V _{GS} = -4V/+18V, V _{DS} = 800V, R _g = 5Ω, I _D = 20A, Inductive Load
Turn-On Rise Time	t _r	—	17.1	—		
Turn-Off Delay Time	t _{d(OFF)}	—	19.6	—		
Turn-Off Fall Time	t _f	—	7.0	—		
Body Diode Reverse-Recovery Time	t _{rR}	—	12.2	—	ns	V _{GS} = -4V, V _{DS} = 800V, I _F = 20A, di/dt = 3600A/μs
Body Diode Reverse-Recovery Charge	Q _{rR}	—	152	—	nC	
Body Diode Reverse-Recovery Current	I _{rRM}	—	20.4	—	A	

- Notes:
- Device mounted on an infinite heatsink.
 - Device mounted on FR-4 substrate PC board, 2oz. copper, with minimum recommended pad layout.
 - Guaranteed by design. Not subject to production testing.
 - Short duration pulse test used to minimize self-heating effect.
 - Drain current limited by maximum junction temperature.




Figure 1. Typical Output Characteristic




Figure 2. Typical Transfer Characteristic




Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage




Figure 4. Typical Transfer Characteristic




Figure 5. Typical On-Resistance vs. Drain Current and Junction Temperature




Figure 6. On-Resistance Variation with Junction Temperature




Figure 7. On-Resistance Variation with Junction Temperature




Figure 8. Gate Threshold Variation vs. Junction Temperature




Figure 9. Diode Forward Voltage vs. Current




Figure 10. Body Diode Characteristic at 25°C




Figure 11. Body Diode Characteristic at -55°C




Figure 12. Body Diode Characteristic at 175°C




Figure 13. Typical Junction Capacitance




Figure 14. Gate Charge




Figure 15. SOA, Safe Operation Area





Figure 16. Transient Thermal Resistance


Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.


TO247 Standard



TO247 Standard			
Dim	Min	Max	Typ
A	4.83	5.21	--
A1	2.10	2.54	--
A2	1.88	2.16	--
b	1.07	1.33	--
b1	1.90	2.41	--
b3	2.87	3.38	--
c	0.51	0.76	0.60
D	20.80	21.75	--
D1	15.88	17.65	--
D2	0.95	1.77	--
E	15.75	16.25	--
E1	12.38	14.52	--
E2	3.68	5.10	--
E3	1.00	2.18	--
E4	13.10	14.52	--
e	5.44 BSC		
L	19.60	20.32	--
L1	3.78	4.40	--
PØ	2.90	3.65	--
S	6.04	6.80	--
T	17.5-20° REF		
W	3.5-4.5° REF		
X	4-5° REF		
All Dimensions in mm			



OPTION A
(TOP VIEW)



OPTION B
(TOP VIEW)

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
All other trademarks are the property of their respective owners.
© 2024 Diodes Incorporated. All Rights Reserved.

www.diodes.com