



500kHz, 18V, 1.5A, Current Mode, DCM/CCM Synchronous DC/DC Buck Converter in TSOT26

Description

The AP65111A is a 500kHz switching frequency internal compensated synchronous DC/DC buck converter. It has integrated low R_{DSON} high and low side MOSFETs.

The AP65111A enables continuous load current of up to 1.5A with efficiency as high as 97%.

The AP65111A implements an automatic custom light load efficiency improvement algorithm.

The AP65111A features current mode control operation, which enables fast transient response times and easy loop stabilization.

- Gaming Consoles
- Flat Screen TV Sets and Monitors
- Set Top Boxes
- · Distributed Power Systems
- · Green Electronics

The AP65111A simplifies board layout and reduces space requirements with its high level of integration and minimal need for external components, making it ideal for distributed power architectures.

The AP65111A is available in a standard Green TSOT26 package and is RoHS compliant.

- · Home Audio
- Consumer Electronics
- Network Systems
- FPGA, DSP and ASIC Supplies

Performance Spec of AP65111AWU-EVM (Rev1)

Parameter	Conditions	Performance Value
Input Voltage	Range 4.5V to 18V	12V
Output Current		1.5A
Output Voltage		3.3V
Transient Response	Peak-to-peak load step from 0.75A to 1.5A	100mV _{P-P}
Switching Frequency		500kHz
Efficiency		92%



500kHz, 18V, 1.5A, Current Mode, DCM/CCM Synchronous DC/DC Buck Converter in TSOT26

Figure 1. Evaluation Board (Rev1)




Figure 2. Load Transient 0.75 to 1.5A




Figure 3. Efficiency (Vout=3.3V)






Figure 4. Efficiency (Vout=5.0V)



PCB Layouts



P62893

O

O

Top Layer

Bottom Layer

AP65111AWU-EVM



500kHz, 18V, 1.5A, Current Mode, DCM/CCM Synchronous DC/DC Buck Converter in TSOT26

Quick Start Guide

The AP65111AWU-EVM has a simple layout and allows access to the appropriate signals through test points. To evaluate the performance of the AP65111A, follow the procedure below:

- 1. Connect a power supply to the input terminals VIN and GND. Set VIN to 12V.
- 2. Connect the positive terminal of the electronic load to Vout and negative terminal to GND.
- 3. EN has a positive voltage through a 100K pull-up to Vin. No supply input is required for EN.
- 4. The evaluation board should now power up with a 3.3V output voltage.
- 5. Check for the proper output voltage of 3.3V (±1%) at the output terminals VouT and GND. Measurement can also be done with a multimeter with the positive and negative leads between VouT and GND.
- 6. Set the load to 1.5A through the electronic load. Check for the stable operation of the SW signal on the oscilloscope. Measure the switching frequency.


Measurement/Performance Guidelines:

- When measuring the output voltage ripple, maintain the shortest possible ground lengths on the oscilloscope probe. Long ground leads can erroneously inject high frequency noise into the measured ripple.
- 2) For efficiency measurements, connect an ammeter in series with the input supply to measure the input current. Connect an electronic load to the output for output current.



500kHz, 18V, 1.5A, Current Mode, DCM/CCM Synchronous DC/DC Buck Converter in TSOT26

EVALUATION BOARD SCHEMATIC



BILL OF MATERIALS

Ref	Value	Description	Qty	Size	Vendor Name	Manufacturer PN
C1,		Ceramic Capacitor,				
C2	22μF	25V, X5R	1	1210	AVX	12103D226KAT2A
		Ceramic Capacitor,				
C3	1μF	16V, X7R, 10%	1	0805	Kemet	C0805C105K4RACTU
		Ceramic Capacitor,				
C4	0.1μF	25V, X7R, 10%	1	0805	Samsung	CL21B104KACNNNC
				10X10X5	Wurth	
L1	6.5µH	DCR=12.5mΩ, Is=10A	1	mm	Electronics	744325650
R1	40.2ΚΩ	Film Resistor, 1%	1	0805	Panasonic	ERJ-6ENF4022V
R2	13ΚΩ	Film Resistor, 1%	1	0805	Panasonic	ERJ-6ENF1302V
R3	59ΚΩ	Film Resistor, 1%	1	0805	Panasonic	ERJ-6ENF5902V
R4	0Ω	Film Resistor, 1%	1	0805	Panasonic	ERJ-6GEY0R00V
R7	100ΚΩ	Film Resistor, 1%	1	0805	Panasonic	ERJ-6ENF1003V
		Terminal Turret Triple			Keystone	
T1	1598	0.094" L (Test Points)	5		Electronics	1598-1
U1		DC/DC converter	1	TSOT26	Diodes	AP65111AWU

ODES

AP65111AWU-EVM

500kHz, 18V, 1.5A, Current Mode, DCM/CCM Synchronous DC/DC Buck Converter in TSOT26

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2017, Diodes Incorporated

www.diodes.com