


## Package Outline Dimensions


W-QFN3030-16 (Type CJ)



W-QFN3030-16 (Type CJ)			
Dim	Min	Max	Typ
A	0.700	0.800	--
A1	0.000	0.050	--
A3	0.203 REF		
b	0.180	0.300	--
D	3.00 BSC		
D2	1.600	1.800	--
E	3.00 BSC		
E2	1.600	1.800	--
e	0.500 TYP		
k	0.200 MIN		
L	0.300	0.500	--
All Dimensions in mm			

## Suggested Pad Layout

W-QFN3030-16 (Type CJ)



Dimensions	Value (in mm)
C	0.500
X	0.350
X1	0.570
X2	1.800
X3	3.300
Y	0.570
Y1	1.800
Y2	3.300

### ALL DIMENSIONS ARE NOMINAL VALUES SHOWN IN MILLIMETERS

Note: The suggested land pattern dimensions have been provided for reference only, as actual pad layouts may vary depending on application. These numbers may be modified based on user equipment capability or fabrication criteria. A more robust pattern may be desired for wave soldering and is calculated by adding 0.2 mm to the 'Z' dimension. For further information, please reference document IPC-7351A, Naming Convention for Standard SMT Land Patterns, and for International grid details, please see document IEC, Publication 97.