

**PI2DPX2023**

**1.8V 20Gbps DP2.1 Linear ReDriver with AUX Listener & Pin Strap Control**

**Features**

- 4-to-4 linear ReDriver™ channel configuration with CTLE gain compensation up to 13.8dB @20Gbps
- Supports 4-lane DP2.1 (UHBR20/UHBR13/UHBR10)/HBR3/HBR2/HBR/RBR
- Ultra low latency (< 300ps) for better interoperability and data throughput
- 4 level controls on CTLE Gain (7.1 to 13.8dB), Flat Gain (-4 to +2dB)
- Integrated AUX channel listener for D3 power saving mode.
- Low Power - DisplayPort active - 324mW typical, D3 power down mode - 1.8mW typical, Disable Power - 27uW typical
- Single Power Supply: 1.8V +/-5%
- Industrial Temperature Support: -40°C to +85°C
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. “Green” Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](#) or your local Diodes representative.  
<https://www.diodes.com/quality/product-definitions/>
- Packaging (Pb-free & Green):
  - Tiny 32-pin, WLGA (FLA) 2.85 x 4.5 mm (0.4 mm pitch, 0.7mm max height)

**Application(s)**

- Graphics Add In Cards
- Laptop, Desktop and AIO PCs
- Workstation and Servers
- Docking Station
- Display Monitors
- Gaming Console
- Active Cables

**Description**

The DIODES™ PI2DPX2023 is a 20Gbps DP2.1/DP1.4 linear ReDriver in a 4-to-4 configuration operated by a 1.8V power supply. The device supports UHBR20 (DP2.1 20Gbps), UHBR13.5 (DP2.1 13.5Gbps), UHBR10 (DP2.1 10Gbps), HBR3 (DP1.4 8.1Gbps), HBR2 (DP1.2 5.4Gbps), HBR(DP1.1 2.7Gbps) and RBR(DP1.0 1.62Gbps) under various DisplayPort speeds. With the on-chip AUX channel listener, the device can automatically monitor the system operation status to enter D3 power saving mode.

The non-blocking linear redriver design ensures that the differential signals conveying pre-shoot and de-emphasis equalization waveforms from the transmitter side to the receiver side help optimize the overall channel link adjustment conducted by the system transmitter and receiver that has been equipped with DFE. The CTLE equalizers are implemented at the inputs of the redriver to compensate the channel loss and reduce the ISI jitters. The flat gain adjustments support the eye diagram opening. The CTLE EQ gains and flat gains are tuned via pin strap control.

**Ordering Information**

Ordering Number	Package Code	Description
PI2DPX2023FLAEX	FLA	32-Pin, W-LGA4528-32

Notes:

- E = Pb-free and Green
- X suffix = Tape/Reel

**Notes:**

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated’s definitions of Halogen- and Antimony-free, “Green” and Lead-free.
3. Halogen- and Antimony-free “Green” products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

*ReDriver is a trademark of Diodes Incorporated.*