



74LVC86A

#### QUADRUPLE 2-INPUT EXCLUSIVE OR GATES

### Description

The 74LVC86A provides four independent 2-input exclusive OR gates. The device is designed for operation with a power supply range of 1.65V to 5.5V. The inputs are tolerant to 5.5V allowing this device to be used in a mixed-voltage environment. The device is fully specified for partial power down applications using  $I_{OFF}$ . The  $I_{OFF}$  circuitry disables the output preventing damaging current backflow when the device is powered down.


The gates perform the positive Boolean function:

$$Y = A \oplus B$$
 or  $Y = \overline{A}B + A\overline{B}$ 

## Features

- Supply Voltage Range from 1.65V to 5.5V
- Sinks 24mA at V<sub>CC</sub> = 3.3V
- CMOS low power consumption
- IOFF Supports Partial-Power-Down Mode Operation
- Inputs or outputs accept up to 5.5V
- Inputs can be driven by 3.3V or 5.5V allowing for voltage translation applications.
- ESD Protection Exceeds JESD 22
  - 200-V Machine Model (A115-A)
  - 2000-V Human Body Model (A114-A)
  - Latch-Up Exceeds 250mA per JESD 78, Class II
  - Exceeds 1000-V Charged Device Model (C101C)
- Range of Package Options SO-14 and TSSOP-14
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/productdefinitions/</u>

**Pin Assignments** 



# Applications

- Voltage level shifting
- General-purpose logic
- Power down signal isolation
- Wide array of products such as:
  - PCs, networking, notebooks, ultrabooks, netbooks
  - Computer peripherals, hard drives, CD/DVD ROM
  - TV, DVD, DVR, set top boxes


- Notes: 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
  - 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
  - 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



# **Pin Descriptions**

Pin Number	Pin Name	Description
1	1A	Data Input
2	1B	Data Input
3	1Y	Data Output
4	2A	Data Input
5	2B	Data Input
6	2Y	Data Output
7	GND	Ground
8	3Y	Data Output
9	ЗA	Data Input
10	3B	Data Input
11	4Y	Data Output
12	4A	Data Input
13	4B	Data Input
14	Vcc	Supply Voltage

# Logic Diagram



# **Function Table**

Inp	Output	
Α	В	Y
L	L	L
L	н	Н
Н	L	Н
н	н	L



Symbol	Description	Rating	Unit
ESD HBM	Human Body Model ESD Protection	2	KV
ESD CDM	Charged Device Model ESD Protection	1	KV
ESD MM	Machine Model ESD Protection	200	V
V <sub>CC</sub>	Supply Voltage Range	-0.5 to 6.5	V
VI	Input Voltage Range	-0.5 to 6.5	V
Vo	Voltage applied to output in high impedance or IOFF state	-0.5 to 6.5	V
Vo	Voltage applied to output in high or low state	-0.3 to V <sub>CC</sub> +0.5	V
I <sub>IK</sub>	Input Clamp Current VI <0	-50	mA
Іок	Output Clamp Current V <sub>O</sub> <0	-50	mA
lo	Continuous output current	50	mA
Icc,, Ignd	Continuous current through Vcc or GND	±100	mA
TJ	Operating Junction Temperature	-40 to +150	°C
T <sub>STG</sub>	Storage Temperature	-65 to +150	°C
Ртот	Total Power Dissipation	500	mW

# Absolute Maximum Ratings (Note 4) (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Note: 4. Stresses beyond the absolute maximum may result in immediate failure or reduced reliability. These are stress values and device operation should be within recommend values.

# Recommended Operating Conditions (Note 5) (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Symbol	Parameter	Conditions	Min	Max	Unit
V <sub>CC</sub>	Supply Voltage	—	1.65	5.50	V
VI	Input Voltage	—	0	5.5	V
N/	Output Valtage	Active Mode	0	V <sub>CC</sub>	V
Vo	Output Voltage	V <sub>CC</sub> = 0V; Power Down Mode	0	5.5	V
A+/A)/	land the shift of the second structure	V <sub>CC</sub> = 1.65V to 2.7V	_	20	
Δt/ΔV I	Input transition rise or fall rate	V <sub>CC</sub> = 2.7V to 5.5V	_	10	ns/V
T <sub>A</sub>	Operating free-air temperature	—	-40	+125	°C

Note: 5. Unused inputs should be held at V<sub>CC</sub> or Ground.



# Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)

0	Demonstration	Test Osnalitions		T <sub>A</sub> = -40°C	C to +85°C	T <sub>A</sub> = -40°C	to +125°C	Unit
Symbol	Parameter	Test Conditions	V <sub>cc</sub>	Min	Max	Min	Max	
		_	1.65V to 1.95V	0.65 X V <sub>CC</sub>		0.65 X V <sub>CC</sub>	_	
	High-level Input	_	2.3V to 2.7V	1.7		1.6		V
VIH	Voltage	—	2.7V to 3.6V	2.0	_	2.0	_	
VIH VIL VOH		_	4.5V to 5.5V	0.7 X V <sub>CC</sub>	—	2.0	—	
		—	1.65V to 1.95V	—	0.35 X V <sub>CC</sub>	—	0.35 X V <sub>CC</sub>	
	Low-level input	_	2.3V to 2.7V	—	0.7	—	0.7	V
VIL	voltage	_	2.7V to 3.6V	—	0.8	—	0.8	v
VIH VIL VOH VOL II IOFF ICC		—	4.5V to 5.5 V	_	0.3 X V <sub>CC</sub>	_	0.3 X V <sub>CC</sub>	
		I <sub>OH</sub> = -100μA	1.65V to 3.6V	V <sub>CC</sub> - 0.2	_	V <sub>CC</sub> – 0.3	_	
V <sub>OH</sub>	High Level Output Voltage	I <sub>OH</sub> = -4mA	1.65V	1.2	—	—	—	v
		I <sub>OH</sub> = -8mA	2.3V	1.9	—	—	—	
		Output Voltage	10	2.7V	2.2	—	2.05	—
			I <sub>OH</sub> = -12mA	3.0V	2.3	—	2.1	—
		I <sub>OH</sub> = -24mA	3.0V	2.2	—	2.0	—	
		I <sub>OH</sub> = 100μA	1.65V to 5.5V	—	0.2	—	0.3	
		$I_{OH} = 4mA$	1.65V	—	0.45	—	0.6	
VIL V VOH C	High-level	I <sub>OH</sub> = 8mA	2.3V	—	0.70	—	0.85	V
VOL	Output Voltage	1. 10m 1	2.7V	—	0.40	—	0.6	v
		I <sub>OH</sub> = 12mA	3.0V	—	0.55	—	0.6	
		I <sub>OH</sub> =-24mA	3.0V	—	0.55	—	0.6	
h	Input Current	V <sub>I</sub> =GND to 5.5V	3.6V	—	±5	—	±20	μA
I <sub>OFF</sub>	Power Down Leakage Current	$V_1$ or $V_0 =$ 0V to 3.6V	0	—	10	_	20	μA
I <sub>CC</sub>	Supply Current	$V_I = GND \text{ or } V_{CC} I_O = 0$	3.6V	—	10	_	40	μA
ΔI <sub>CC</sub>	Additional Supply Current	One input at V <sub>CC</sub> –0.6V Other	2.7V to 3.6V	_	500	_	5000	μA



# **Switching Characteristics**

	Deremeter	Test Conditions	V <sub>cc</sub>	T	T <sub>A</sub> = +25°C		-40°C to +85°C		-40°C to +125°C		Unit
	Parameter			Min	Тур	Max	Min	Max	Min	Max	Unit
Propagation		1.65V to1.95V	1.0	4.1	9.4	1.0	9.9	1.0	11.4		
	1 0	Figure 1	2.3V to 2.7V	1.0	2.9	7.1	1.0	7.6	1.0	9.7	ns
τpd	Delay A <sub>N</sub> or B <sub>N</sub> to Y <sub>N</sub>		2.7V	1.0	2.8	5.4	1.0	5.6	1.0	7.1	
	to Y <sub>N</sub>		3.0V to 3.6V	1.0	2.5	4.4	1.0	4.6	1.0	5.8	
t <sub>SK(0)</sub>	Output Skew Time	_	3.0V to 3.6V	_	_	_	_	1.0	_	1.5	ns

# **Operating Characteristics** (@T<sub>A</sub> = +25°C, unless otherwise specified.)

	Parameter	Test Conditions	V <sub>CC</sub> = 1.8V Typ	V <sub>CC</sub> = 2.5V Typ	V <sub>CC</sub> = 3.3V Typ	Unit
$C_{\text{pd}}$	Power dissipation capacitance per gate	f = 10 MHz	6.4	7.4	8.4	pF
Cı	Input Capacitance	$V_i = V_{CC} - or$ GND	4	4	4	pF


# **Package Characteristics**

Symbol	Parameter	Test Conditions	V <sub>cc</sub>	Min	Тур	Max	Unit
0	Thermal Resistance	SO-14		—	TBD	_	°C/W
θ <sub>JA</sub>	Junction-to-Ambient	TSSOP-14	(Note 6)	_	159	—	
	Thermal Resistance	SO-14		_	TBD	—	0000
θ <sub>JC</sub>	Junction-to-Case	TSSOP-14	(Note 6)		25	_	°C/W


Note: 6. Test condition for SO-14 and TSSOP-14: Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.




## **Parameter Measurement Information**



V <sub>cc</sub>	Inputs		v	C	Р
	VI	t <sub>r</sub> /t <sub>f</sub>	V <sub>M</sub>	C∟	RL
1.8V±0.15V	V <sub>CC</sub>	≤2ns	V <sub>CC</sub> /2	30pF	1ΚΩ
2.5V±0.2V	Vcc	≤2ns	V <sub>CC</sub> /2	30pF	500Ω
2.7V	2.7V	≤2.5ns	1.5V	50pF	500Ω
3.3V±0.3V	2.7V	≤2.5ns	1.5V	50pF	500Ω



Voltage Waveform Pulse Duration



#### **Voltage Waveform Propagation Delay Times** Inverting and Non Inverting Outputs


Notes:

- A . Includes test lead and test apparatus capacitance. B. All pulses are supplied at pulse repetition rate  $\leq$  10 MHz C. Inputs are measured separately one transition per measurement D. t<sub>PLH</sub> and t<sub>PHL</sub> are the same as t<sub>PD</sub>

Figure 1. Load Circuit and Voltage Waveforms




# **Ordering Information**



Note: 7. The taping orientation and tape details can be found at http://www.diodes.com/datasheets/ap02007.pdf

# **Marking Information**

#### (1) SO-14, TSSOP-14




 $\underline{YY} : Year : 08, 09, 10 \sim$  $\underline{WW} : Week : 01 \sim 52; 52$ represents 52 and 53 week  $\underline{X} : Internal Code$ 

Part Number	Package
74LVC86AS14	SO-14
74LVC86AT14	TSSOP-14



# Package Outline Dimensions (All dimensions in mm.)

Please see http://www.diodes.com/package-outlines.html for the latest version.



	SO-14				
Dim	Min	Max			
Α	1.47	1.73			
A1	0.10	0.25			
A2	1.45	Тур			
в	0.33	0.51			
D	8.53	8.74			
Е	3.80	3.99			
е	1.27	Тур			
Н	5.80	6.20			
L	0.38	1.27			
θ	0°	8°			
All Di	mension	s in mm			

	-
Pin#1 Indent	ne

TSSOP-14


SO-14

TSSOP-14		
Dim	Min	Max
a1	7° (4X)	
a2	0°	8°
Α	4.9	5.10
в	4.30	4.50
С	-	1.2
D	0.8	1.05
F	1.00 Typ	
F1	0.45	0.75
G	0.65 Typ	
ĸ	0.19	0.30
L	6.40 Тур	
All Dimensions in mm		



# **Suggested Pad Layout**


Please see http://www.diodes.com/package-outlines.html for the latest version.



SO-14

Dimensions	Value (in mm)
Х	0.60
Y	1.50
C1	5.4
C2	1.27

TSSOP-14



Dimensions	Value (in mm)
Х	0.45
Y	1.45
C1	5.9
C2	0.65



#### IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

provided Diodes' products are subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners. © 2023 Diodes Incorporated. All Rights Reserved.

#### www.diodes.com