



HIGH SENSITIVITY CMOS HALL-EFFECT LATCH

Description

The AH920 is a Hall-effect latch designed in mixed signal CMOS technology. It is quite suitable for use in automotive, industrial and consumer applications.

Superior high-temperature performance is made possible through dynamic offset cancellation, which reduces the residual offset voltage normally caused by device over-molding, temperature dependencies, and thermal stress. The device integrates a voltage regulator, Hallvoltage generator, small-signal amplifier, chopper stabilization, schmitt trigger, and open-drain output.


An on-board regulator permits operation with supply voltage from 3.5V to 20V.

The AH920 is available in TO-92S-3 and SOT-23-3 packages, which are optimized for most applications.

Features

- Wide Operating Voltage Range from 3.5V to 20V
- Symmetrical Switch Points
- Chopper-Stabilized Amplifier Stage
- Superior Temperature Stability
- Open-Drain Output
- Wide Operating Temperature Range: -40°C to +125°C
- ESD Rating: 6000V (Human Body Model)
- Totally Lead-free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3

Pin Assignments



Applications


- Brushless DC Motor Commutation
- Brushless DC Fan
- Solid-State Switch
- Revolution Counting
- Speed Detection
 - High Sensitivity and Unconnected Switch


Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.

- See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

Typical Applications Circuit








Pin Descriptions

Pin Number		Din Nome	Function			
TO-92S-3	SOT-23-3	- Pin Name Function			Pin Name	Function
1	1	VCC	Supply voltage			
2	3	GND	Ground pin			
3	2	OUT	Output Pin			

Functional Block Diagram





Absolute Maximum Ratings (Note 4)

Symbol	Parameter	Rating	Unit
V _{CC}	Supply Voltage	20	V
I _{CC}	Supply Current (Fault)	5	mA
I _{OUT}	Output Current (Continuous)	25	mA
6	Power Dissipation	TO-92S-3 400	mW
PD		SOT-23-3 230	
T _A	Operation Temperature	-50 to +150	°C
T _{STG}	Storage Temperature	-65 to +150	°C
T _{J (} Max)	Maximum Junction Temperature	+165	°C
ESD	ESD (Human Body Model)	6000	V

Note 4: Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to "Absolute Maximum Ratings" for extended periods may affect device reliability.

Recommended Operating Conditions

Symbol	Parameter	Min	Мах	Unit	
Vcc	Supply Voltage	3.5	20	V	
T _A	Operating Ambient Temperature	-40	+125	°C	

Electrical Characteristics (@V_{CC}=12V, T_A=+25°C, unless otherwise specified. Notes 5 & 6)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
lcc	Supply Current	B <b<sub>RP</b<sub>	-	3.0	5.0	mA
		B>B _{OP}	-	3.0	5.0	
		V _{CC} =3.5V, I _{OUT} =5mA, B>B _{OP} (Note 7)	-	45	120	mV
VSAT	Saturation Voltage	I _{OUT} =20mA, B>B _{OP} (Note 7)	_	185	500	mV
		V _{CC} =20V, I _{OUT} =20mA, B>B _{OP} (Note 7)	-	185	500	mV
I _{LEAKAGE}	Output Leakage Current	V _{OUT} =20V, B <b<sub>RP (Note 8)</b<sub>	-	0.1	10	μA
trising	Output Rising Time	R _L =1kΩ, C _L =20pF	-	0.4	2	μs
tFALLING	Output Falling Time	$R_L=1k\Omega$, $C_L=20pF$	-	0.4	2	μs

Notes: 5. Output initial status is low when powering on.

6. The supply current I_{CC} represents the average supply current. The output is open during measurement.


7. The device is put under the magnetic field: $B{>}B_{OP}$

8. The device is put under the magnetic field: $\mathsf{B}{<}\mathsf{B}_{\mathsf{RP}}$



Magnetic Characteristics (@V_{CC}=12V, T_A=+25°C, unless otherwise specified.)

Symbol	Parameter	Min	Тур	Мах	Unit
B _{OP}	Operating Point	5	22	40	Gauss
B _{RP}	Releasing Point	-40	-22	-5	Gauss
B _{HYS}	Hysteresis	-	45		Gauss





Magnetic Characteristics (Cont.)




Table 1. Output Status vs. Magnetic Pole



Magnetic Characteristics (Cont.)





Figure 4. Test Circuit of AH920




Test Circuit and Test Conditions (Cont.)






Test Circuit and Test Conditions (Cont.)






Performance Characteristics (Cont.)






Ordering Information





Package Outline Dimensions (All dimensions in mm(inch).)


(1) Package Type: TO-92S-3





Package Outline Dimensions (All dimensions in mm(inch). Cont.)


(2) Package Type: SOT-23-3





Suggested Pad Layout

(1) Package Type: SOT-23-3





IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2017, Diodes Incorporated

www.diodes.com