



APR34910

SECONDARY SIDE SYNCHRONOUS RECTIFICATION SWITCHER

Description


The APR34910 is a secondary-side combo IC combining an N-channel MOSFET and a driver circuit designed for synchronous rectification (SR).

The APR34910 supports continuous and discontinuous conduction mode (CCM and DCM) and quasi-resonant flyback operation. It not only provides a short turn-on and turn-off delay to reduce power loss, but also eliminates false trigger to keep safe operation without adding any external components or circuitry.

The APR34910 can be charged by internal PLR (Pulse Linear Regulator) at low system output voltage and can provide a wide output operation voltage from 3.3V to 24V.

The APR34910 is available in the SO-8 (Type CJ2) package.

Pin Assignments



Features

- Supports Flyback Synchronous Rectification with CCM/DCM/QR Operation Mode
- Intelligent Control to Minimize Turn-On and Turn-Off Delay
- Smart-Blanking Control to Prevent Shoot Through
- Support Both High-Side and Low-Side Application
- Built-in PLR Power Supply for Low System Output Voltage
- Internal UVLO Protection
- Fewest External Components
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Applications


- Smart phone quick chargers
- Notebook computer adaptors
- Set-top box (STB) power supplies
- Other compact switching AC-DC adaptors/chargers

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Typical Applications Circuit




Pin Descriptions

Pin Number	Pin Name	Function	
1	VDD	Supply input. It provides bias voltage for the internal logic circuit and the MOSFET driver.	
2	VDET	MOSFET drain sensing	
3,4	GND	Ground, also used as FET source sense reference for DRAIN	
5, 6, 7, 8	DRAIN	Synchronous rectification MOSFET drain voltage sense input	



Functional Block Diagram





Absolute Maximum Ratings (Note 4)

Symbol	Parameter	Rating	Unit
V_{DD}	Voltage at VDD Pin	-0.3 to 7	٧
V _{DRAIN} , V _V DET	Voltage at DRAIN Pin and VDET pin	-0.7 to 100	٧
P _D	Power Dissipation at T _A = +25°C	0.6	W
TJ	Operating Junction Temperature(Note 6)	+150	°C
T _{STG}	Storage Temperature	-65 to +150	°C
T _{LEAD}	Lead Temperature (Soldering, 10s)	+300	°C
θЈА	Thermal Resistance (Junction to Ambient) (Note 5)	78	°C/W
θ _{JC}	Thermal Resistance (Junction to Case) (Note 5)	7	°C/W
	Human Body Model	4000	V
ESD	Charged Device Model	1500	V

Notes:

Stresses greater than those listed under Absolute Maximum Ratings can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions is not implied. Exposure to Absolute Maximum Ratings for extended periods can affect device reliability.
Test condition: Device mounted on FR-4 substrate PC board, 1mm width, 20mm length, 2oz power lead.
Setting +85°C in the aging condition.



Electrical Characteristics (@ $V_{OUT} = 5V$, $T_A = -40$ °C $< T_A < +85$ °C, unless otherwise specified.)

Symbol	Parameter	Condition	Min	Тур	Max	Unit	
Internal Supply Sec	Internal Supply Section (VDD Pin)						
V _{DD_ON}	VDD ON Threshold Voltage	_	3.55	3.75	3.95	V	
V_{DD_OFF}	VDD Off Threshold Voltage	_	3.35	3.55	3.75	V	
V_{DD_REG}	VDD Regulation Voltage	V _{OUT} = 3V, V _{DRAIN} = 12V	5.3	5.7	6.5	V	
I_{Q_VDD}	Quiescent Current	V _{DD} = 5.0V	_	190	255	μΑ	
MOSFET Section (V	MOSFET Section (VDET Pin)						
V _{ON_TH}	Turn-On Threshold Voltage	Voltage at VDET Pin	-225	-200	-175	mV	
V _{ON_REG}	Turn-On Regulation Voltage(Note 7)	Voltage at VDET Pin	_	-40	_	mV	
Von_off	Turn-Off Threshold Voltage(Note 7)	Voltage at VDET Pin	_	-7	_	mV	
I _{CHG_VDD}	VDET to VDD Maximum Charging Current	_	50	_	105	mA	
Control Section	Control Section						
t _{ON_MIN}	GATE Minimum On Time	_	0.60	0.9	1.2	μs	
t _{D_ON}	Turn-On Delay(Note 7)	C _{LOAD} = 2.2nF	_	30	_	ns	
t _{D_OFF}	Turn-Off Propagation Delay(Note 7)	_	_	15	_	ns	

Note:

7. Guaranteed by design.



Electrical Characteristics (continued)

MOSFET Static Characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V _{DSS(BR)}	Drain to Source Breakdown Voltage	$V_{GS} = 0V, I_D = 0.25mA$	100	_	_	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 80V, V _{GS} = 0V	_	_	0.4	μΑ
R _{DS(ON)}	Drain to Source On-state Resistance	$V_{GS} = 4.5V, I_D = 2A$	_	10	_	mΩ
V _{SD}	Diode Forward Voltage	V _{GS} = 0V, I _S = 2A	_	0.7	1.1	V
t _{RR}	Body Diode Reverse Recovery Time	$I_F = 20A$, di/dt = 100A/ μ s	_	44.3	_	ns
Q _{RR}	Body Diode Reverse Recovery Charge	I _F = 20A, di/dt = 100A/μs	_	65.5	_	nC

MOSFET Dynamic Characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
C _{iss}	Input Capacitance		_	2309	_	
Coss	Output Capacitance	$V_{GS} = 0V, V_{DS} = 50V,$ f = 1MHz	_	536	_	pF
C _{rss}	Reverse Transfer Capacitance		_	13.7	_	
Q_gs	Gate to Source Charge		_	7.0	_	
Q_{gd}	Gate to Drain Charge (Miller Charger)	$V_{DD} = 50V, I_D = 20A$	_	8.5	_	nC
Qg	Total Gate Charge	V _{GS} = 4.5V	_	20.2	_	
R _g	Gate Resistance	V _{DS} = 0V, V _{GS} = 0V, f = 1MHz	_	1.9	_	Ω



Operation Description

VDD Regulator and UVLO Protection

The VDD is supplied by PLR (Pulse Linear Regulator) from the drain voltage. The APR34910 can be charged by internal PLR (Pulse Linear Regulator) at low system output voltage as low as 0V.

When VDD provides bias voltage for the controller. A capacitor (typical 3.3µF) should be connected between the VDD pin and GND pin. The APR34910 also has UVLO protection. When V_{DD} drops below V_{DD} UVLO, the IC will stop providing gate drive pulse.

GATE Turn-On Logic

The APR34910 determines the synchronous rectification MOSFET turning-on time by monitoring the MOSFET drain-to-source voltage. When the drain voltage is lower than the turn-on threshold voltage V_{ON_TH} , the IC outputs a positive drive voltage after a turn-on delay time (t_{D_ON}). The MOSFET will then turn on and the current will transfer from the body diode into the MOSFET's channel.

GATE Voltage Regulation/Auto-Tracking

A minimum on-time (t_{ON_MIN}) blanking period aims to prevent accidental turn-off due to interference of ringing noise voltage. When the controlled MOSFET gate turns on, some ringing noise will be generated. Utilizing a minimum on-time timer to blank the V_{THOFF} comparator keeps the SR MOSFET on for at least the minimum on-time. During this period, the gate driver can still be quickly pulled down to zero when the V_{DRAIN} ringing voltage goes over 2V.

Once the synchronous rectification gate outputs a high level voltage, the secondary-side current goes through synchronous rectification MOSFET. The voltage dropping on the MOSFET is calculated by $R_{DS(ON)} \times$ secondary-side current. After minimum turn-on time t_{ON_MIN} , the IC continuously monitors V_{DRAIN} by the DRAIN pin and generates a pull-down current from the MOSFET gate until drain voltage equals to -40mV. As shown in Figure 1, the MOSFET drain-to-source voltage would remain around -40mV (V_{ON} REG) with the secondary-side current decreasing.



Operation Description (continued)




Figure 1. Forward Regulation Operation Principle

Smart-Blanking Control

Because of the resonance oscillation of primary inductance and equivalent output capacitance of the switching device, the voltage on the MOSFET drain pin has an under-damped voltage ring in DCM operation mode. In special occasions, such as output transition period or light-load conditions, the ring of the V_{DRAIN} will meet conduction requirement and the SR MOSFET will turn on falsely during the Toff period. When the turn—on of the primary MOSFET meets the false turn-on of the SR, there will be an immediate shoot-through of the transformer. To avoid such faults, the device utilizes a built-in smart-blanking function to prevent continuous false turn-on. When detecting false turn-on at least twice during a period of 4µs in the Toff time period, the SR gate driver will be blanked for a period of 20µs. Figure 2 shows the smart-blanking control method.





Figure 2. Smart-blanking Control Method

GATE Turn-Off Logic

When the V_{DRAIN} rises to the turn-off threshold (-7mV), the synchronous rectification MOSFET gate voltage will be quickly pulled down from a low voltage to zero after a very short turn-off delay. For CCM mode, when the primary MOSFET turns on, the secondary V_{DRAIN} will rise up in the meantime. Once drain voltage rises to the turn-off threshold, the gate-driving signal will be immediately shut down.




Ordering Information



				13"Tape and Reel	
Package	Temperature Range	Part Number	Marking ID	Quantity	Part Number Suffix
SO-8 (Type CJ2)	-40 to +85°C	APR34910S-13	34910	4000/Tape and Reel	-13

Marking Information

SO-8 (Type CJ2)






Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SO-8 (Type CJ2)




S	SO-8 (Type CJ2)				
Dim	Min	Max	Тур		
Α	1.450	1.750			
A1	0.100	0.250			
A2	1.350	1.550			
b	0.330	0.510			
С	0.170	0.250			
D	4.700	5.100			
Е	5.800	6.200			
E1	3.800	4.000			
е	1.27 BSC				
L	0.400	1.270			
Α	0°	8°			
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SO-8 (Type CJ2)



Di	Value		
Dimensions	(in mm)		
С	1.270		
G	3.500		
G1	1.750		
Х	0.820		
X1	4.630		
Y	1.500		
Y1	6.500		

Mechanical Data

- Moisture Sensitivity: MSL Level 3 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per JESD22-B102 @3
- Weight: 0.078719 grams (Approximate)



IMPORTANT NOTICE

- DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, guality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with
- Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and
- Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- Diodes products are provided subject to Diodes' Standard Terms (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2022 Diodes Incorporated

www.diodes.com

11 of 11 APR34910 January 2022 www.diodes.com © Diodes Incorporated Document number: DS43209 Rev. 4 - 2