

APSMBJ SERIES

**SURFACE-MOUNT
UNIDIRECTIONAL AND BIDIRECTIONAL
TRANSIENT VOLTAGE SUPPRESSORS**

**REVERSE VOLTAGE - 6.8 to 82 Volts
POWER DISSIPATION 600 Watts**


FEATURES

- For surface-mounted applications
- Reliable low cost construction utilizing molded plastic technique
- Typical IR less than 1 μ A above 10V
- Fast response time: typically less than 1.0ns for Unidirection, less than 5.0ns for Bidirection, from 0 Volts to BV min
- RoHS compliant
- AEC-Q101 qualified
- PPAP capable
- Automotive grade
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**

MECHANICAL DATA

- Package: Molded plastic
- Package Material: Molding compound, UL Flammability classification 94V-0, (No Br. Sb. Cl.) "Halogen-free"
- Polarity: Cathode band denotes unidirectional device; none cathode band denotes bidirectional device
- Moisture Sensitivity: Max Soldering Temperature +260°C for 30 secs as per JEDECJ-STD-020
- Terminals Finish: Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208
- Weight: 0.003 ounces, 0.093 gram (Approximate)

SMB



| SMB | | |
|------|------|------|
| DIM. | MIN. | MAX. |
| A | 4.06 | 4.57 |
| B | 3.30 | 3.94 |
| C | 1.96 | 2.21 |
| D | 0.15 | 0.31 |
| E | 5.21 | 5.59 |
| F | 0.05 | 0.20 |
| G | 2.01 | 2.50 |
| H | 0.76 | 1.52 |

All Dimensions in millimeter

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at +25°C ambient temperature unless otherwise specified.

ABSOLUTE RATINGS

| PARAMETER | SYMBOL | VALUE | UNIT |
|---|-------------|-------------|------|
| Peak Power Dissipation at $T_A = +25^\circ\text{C}$, $t_P = 1\text{ms}$ (Note 4) | P_{PK} | 600 | W |
| Peak Forward Surge Current 8.3ms Single Half Sine Wave @ $T_J = +25^\circ\text{C}$ (Note 5) | I_{FSM} | 90 | A |
| Steady State Power Dissipation with PCB | $P_{M(AV)}$ | 1.5 | W |
| Maximum Instantaneous Forward Voltage at 16A (Notes 5, 6) | V_F | 2.5 | V |
| Operating Temperature Range | T_J | -55 to +175 | °C |
| Storage Temperature Range | T_{STG} | -55 to +175 | °C |

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
4. Non-repetitive current pulse, per fig. 5 and derated above $T_J = +25^\circ\text{C}$, per fig. 1.
5. Only for unidirectional units.
6. $V_F \text{ max} = 2.0\text{V}$ at $I_F = 16\text{A}$ 300 μ s square wave pulse.







ELECTRICAL CHARACTERISTICS

| Device Unidirectional | Device Bidirectional | Device Marking Code | | Reverse Standoff Voltage VR (V) | Breakdown Voltage VBR Volts | | | Max. Clamping Voltage @IPP VC (V) | Max. Peak Pulse Current IPP (A) | Max. Reverse Leakage @ VR IR (µA) |
|-----------------------|----------------------|---------------------|-------|------------------------------------|-----------------------------|-------|----------|--------------------------------------|------------------------------------|--------------------------------------|
| | | (UNI) | (BI) | | Min. | Max. | @It (mA) | | | |
| APSMBJ6.8A | APSMBJ6.8CA | A6V8A | A6V8C | 5.8 | 6.45 | 7.13 | 10 | 10.5 | 57.1 | 1000 |
| APSMBJ7.5A | APSMBJ7.5CA | A7V5A | A7V5C | 6.4 | 7.13 | 7.88 | 10 | 11.3 | 53.1 | 500 |
| APSMBJ8.2A | APSMBJ8.2CA | A8V2A | A8V2C | 7.0 | 7.79 | 8.61 | 10 | 12.1 | 49.6 | 200 |
| APSMBJ9.1A | APSMBJ9.1CA | A9V1A | A9V1C | 7.8 | 8.65 | 9.56 | 1.0 | 13.4 | 44.8 | 50 |
| APSMBJ10A | APSMBJ10CA | A10A | A10C | 8.6 | 9.50 | 10.50 | 1.0 | 14.5 | 41.4 | 10 |
| APSMBJ11A | APSMBJ11CA | A11A | A11C | 9.4 | 10.5 | 11.6 | 1.0 | 15.6 | 38.5 | 5.0 |
| APSMBJ12A | APSMBJ12CA | A12A | A12C | 10.2 | 11.4 | 12.6 | 1.0 | 16.7 | 35.9 | 0.5 |
| APSMBJ13A | APSMBJ13CA | A13A | A13C | 11.1 | 12.4 | 13.7 | 1.0 | 18.2 | 33.0 | 0.5 |
| APSMBJ15A | APSMBJ15CA | A15A | A15C | 12.8 | 14.3 | 15.8 | 1.0 | 21.2 | 28.3 | 0.5 |
| APSMBJ16A | APSMBJ16CA | A16A | A16C | 13.6 | 15.2 | 16.8 | 1.0 | 22.5 | 26.7 | 0.5 |
| APSMBJ18A | APSMBJ18CA | A18A | A18C | 15.3 | 17.1 | 18.9 | 1.0 | 25.2 | 23.8 | 0.5 |
| APSMBJ20A | APSMBJ20CA | A20A | A20C | 17.1 | 19.0 | 21.0 | 1.0 | 27.7 | 21.7 | 0.5 |
| APSMBJ22A | APSMBJ22CA | A22A | A22C | 18.8 | 20.9 | 23.1 | 1.0 | 30.6 | 19.6 | 0.5 |
| APSMBJ24A | APSMBJ24CA | A24A | A24C | 20.5 | 22.8 | 25.2 | 1.0 | 33.2 | 18.1 | 0.5 |
| APSMBJ27A | APSMBJ27CA | A27A | A27C | 23.1 | 25.7 | 28.4 | 1.0 | 37.5 | 16.0 | 0.5 |
| APSMBJ30A | APSMBJ30CA | A30A | A30C | 25.6 | 28.5 | 31.5 | 1.0 | 41.4 | 14.5 | 0.5 |
| APSMBJ33A | APSMBJ33CA | A33A | A33C | 28.2 | 31.4 | 34.7 | 1.0 | 45.7 | 13.1 | 0.5 |
| APSMBJ33A | APSMBJ33CAC | A33A | A33CC | 28.2 | 31.4 | 34.7 | 1.0 | 45.7 | 13.1 | 0.5 |
| APSMBJ36A | APSMBJ36CA | A36A | A36C | 30.8 | 34.2 | 37.8 | 1.0 | 49.9 | 12.0 | 0.5 |
| APSMBJ39A | APSMBJ39CA | A39A | A39C | 33.3 | 37.1 | 41.0 | 1.0 | 53.9 | 11.1 | 0.5 |
| APSMBJ43A | APSMBJ43CA | A43A | A43C | 36.8 | 40.9 | 45.2 | 1.0 | 59.3 | 10.1 | 0.5 |
| APSMBJ47A | APSMBJ47CA | A47A | A47C | 40.2 | 44.7 | 49.4 | 1.0 | 64.8 | 9.3 | 0.5 |
| APSMBJ51A | APSMBJ51CA | A51A | A51C | 43.6 | 48.5 | 53.6 | 1.0 | 70.1 | 8.6 | 0.5 |
| APSMBJ56A | APSMBJ56CA | A56A | A56C | 47.8 | 53.2 | 58.8 | 1.0 | 77.0 | 7.8 | 0.5 |
| APSMBJ62A | APSMBJ62CA | A62A | A62C | 53.0 | 58.9 | 65.1 | 1.0 | 85.0 | 7.1 | 0.5 |
| APSMBJ68A | APSMBJ68CA | A68A | A68C | 58.1 | 64.6 | 71.4 | 1.0 | 92.0 | 6.5 | 0.5 |
| APSMBJ75A | APSMBJ75CA | A75A | A75C | 64.7 | 71.3 | 78.8 | 1.0 | 103.0 | 5.8 | 0.5 |
| APSMBJ82A | APSMBJ82CA | A82A | A82C | 70.1 | 77.9 | 86.1 | 1.0 | 113.0 | 5.3 | 0.5 |

Notes:

- 7. Suffix 'A' denotes 5% tolerance device.
- 8. Add suffix 'C' or 'CA' after part number to specify Bidirectional devices.
- 9. The IR limit is double for Bidirectional devices.
- 10. APSMBJ33CA for special customer used.


RATING AND CHARACTERISTIC CURVES
APSMBJ SERIES



Ordering Information :

| Part Number | Package | Packing | |
|---------------|---------|---------|---------|
| | | Qty. | Carrier |
| APSMBJ SERIES | SMB | 3000pcs | Reel |

Marking Information :




XXXX : Assembly Tracing Code
ZZZ : Product Type Marking Code
Bar Denotes Cathode Side

Packaging Information :

| DEVICE | QTY./REEL (PCS) | REEL DIA. (INCH) | QTY./BOX (PCS) | QTY./CARTON (PCS) |
|-------------------------|--------------------|---------------------|-------------------|----------------------|
| APSMBJXXA APSMBJXXCA | 3000 | 13 | 6k | 36k |

Suggested Pad Layout :

SMB



| Dimensions | Value (in mm) |
|------------|------------------|
| C | 4.30 |
| G | 1.80 |
| X | 2.50 |
| X1 | 6.80 |
| Y | 2.30 |

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
All other trademarks are the property of their respective owners.
© 2023 Diodes Incorporated. All Rights Reserved.

www.diodes.com