

SOT223 PNP SILICON PLANAR HIGH VOLTAGE TRANSISTOR


BSP16

ISSUE 3 – AUGUST 1995
FEATURES

- * High V_{CEO}
- * Low saturation voltage

COMPLEMENTARY TYPE: – BSP19

PARTMARKING DETAIL: – BSP16


ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	V_{CBO}	-350	V
Collector-Emitter Voltage	V_{CEO}	-300	V
Emitter-Base Voltage	V_{EBO}	-6	V
Peak Pulse Current	I_{CM}	-1	A
Continuous Collector Current	I_C	-0.5	A
Power Dissipation at $T_{amb}=25^{\circ}C$	P_{tot}	2	W
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 to +150	$^{\circ}C$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^{\circ}C$ unless otherwise stated).

PARAMETER	SYMBOL	MIN.	MAX.	UNIT	CONDITIONS.
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	-350		V	$I_C = -100\mu A$
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	-300		V	$I_C = -10mA$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	-5		V	$I_E = -100\mu A$
Collector Cut-Off Current	I_{CBO}		-1	μA	$V_{CB} = -280V$
Emitter Cut-Off Current	I_{EBO}		-20	μA	$V_{EB} = -6V$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$		-2.0 -0.5	V V	$I_C = -50mA, I_B = -5mA^*$ $I_C = -30mA, I_B = -3mA^*$
Static Forward Current Transfer Ratio	h_{FE}	30	120		$I_C = -50mA, V_{CE} = -10V^*$
Transition Frequency	f_T	15		MHz	$I_C = -10mA, V_{CE} = -10V^*$ $f = 30MHz$
Output Capacitance	C_{obo}		15	pF	$V_{CB} = -10V, f = 1MHz$

 *Measured under pulsed conditions. Pulse width=300 μs . Duty cycle $\leq 2\%$

For typical characteristics graphs see FMMTA92 datasheet.