

Product Summary

| BV _{DSS} | R _{DS(ON)} Max | I _D T _A = +25°C |
|-------------------|-------------------------------|--|
| -30V | 16mΩ @ V _{GS} = -20V | -7.3A |
| | 20mΩ @ V _{GS} = -10V | -6.0A |

Description

This new generation MOSFET has been designed to minimize the on-state resistance (R_{DS(ON)}) yet maintain superior switching performance, making it ideal for high-efficiency power management applications.

Applications


- DC-DC converters
- Power management functions
- Backlighting

Features

- Low On-Resistance
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen- and Antimony-Free. "Green" Device (Note 3)**
- **For automotive applications requiring specific change control (i.e.: parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please refer to the related automotive grade (Q-suffix) part. A listing can be found at <https://www.diodes.com/products/automotive/automotive-products/>.**
- **This part is qualified to JEDEC standards (as references in AEC-Q) for High Reliability. <https://www.diodes.com/quality/product-definitions/>**

Mechanical Data

- Package: SO-8
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminal Connections Indicator: See Diagram
- Terminals: Finish – Matte Tin Annealed over Copper Lead-Frame. Solderable per MIL-STD-202, Method 208 (e3)
- Weight: 0.074 grams (Approximate)




Ordering Information (Note 4)

| Part Number | Package | Packing | |
|---------------|---------|---------|-------------|
| | | Qty. | Carrier |
| DMG4435SSS-13 | SO-8 | 2500 | Tape & Reel |

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
 2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
 4. For packaging details, go to our website at <https://www.diodes.com/design/support/packaging/diodes-packaging/>.

Marking Information



D||| = Manufacturer's Marking
G4435SS = Product Type Marking Code
YYWW = Date Code Marking
YY or **YY** = Year (ex: 22 = 2020)
WW or **WW** = Week (01 to 53)

Maximum Ratings (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

| Characteristic | | | Symbol | Value | Unit |
|--|------------------|--|-----------|--------------|------|
| Drain-Source Voltage | | | V_{DSS} | -30 | V |
| Gate-Source Voltage | | | V_{GSS} | ± 25 | V |
| Continuous Drain Current (Note 5) $V_{GS} = -20$ | Steady State | $T_A = +25^\circ\text{C}$ $T_A = +70^\circ\text{C}$ | I_D | -7.3 -5.7 | A |
| | $t < 10\text{s}$ | $T_A = +25^\circ\text{C}$ $T_A = +70^\circ\text{C}$ | I_D | -10 -7.5 | A |
| Pulsed Drain Current (Note 6) | | | I_{DM} | -80 | A |

Thermal Characteristics

| Characteristic | | Symbol | Value | Unit |
|---|---------------------------|-----------------|-------------|--------------------|
| Power Dissipation (Note 5) | $T_A = +25^\circ\text{C}$ | P_D | 2.5 | W |
| | $T_A = +70^\circ\text{C}$ | | 1.5 | W |
| Thermal Resistance, Junction to Ambient @ $T_A = +25^\circ\text{C}$ | Steady State | $R_{\theta JA}$ | 96.5 | $^\circ\text{C/W}$ |
| | $t < 10\text{s}$ | | 55 | $^\circ\text{C/W}$ |
| Operating and Storage Temperature Range | | T_J, T_{STG} | -55 to +150 | $^\circ\text{C}$ |

Notes: 5. Device mounted on .1in. x 1in. FR-4 PCB with 2oz. copper, and the testing is based on the $t < 10\text{s}$. The value in any given application depends on the user's specific board design.
 6. Repetitive rating, pulse width limited by junction temperature.

Electrical Characteristics (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

| Characteristic | Symbol | Min | Typ | Max | Unit | Test Condition |
|---|--------------|------|-------|-----------|---------------|--|
| OFF CHARACTERISTICS (Note 7) | | | | | | |
| Drain-Source Breakdown Voltage | BV_{DSS} | -30 | — | — | V | $V_{GS} = 0V, I_D = -1mA$ |
| Zero Gate Voltage Drain Current $T_J = +25^\circ\text{C}$ | I_{DSS} | — | — | -1.0 | μA | $V_{DS} = -30V, V_{GS} = 0V$ |
| Gate-Source Leakage | I_{GSS} | — | — | ± 100 | nA | $V_{GS} = \pm 25V, V_{DS} = 0V$ |
| ON CHARACTERISTICS (Note 7) | | | | | | |
| Gate Threshold Voltage | $V_{GS(TH)}$ | -1.0 | -1.7 | -2.5 | V | $V_{DS} = V_{GS}, I_D = -250\mu\text{A}$ |
| Static Drain-Source On-Resistance | $R_{DS(ON)}$ | — | 13 | 16 | m Ω | $V_{GS} = -20V, I_D = -11A$ |
| | | | 15 | 20 | | $V_{GS} = -10V, I_D = -10A$ |
| | | | 21 | 29 | | $V_{GS} = -5V, I_D = -5A$ |
| Forward Transfer Admittance | $ Y_{fs} $ | — | 22 | — | S | $V_{DS} = -5V, I_D = -10A$ |
| Diode Forward Voltage | V_{SD} | — | -0.74 | -1.0 | V | $V_{GS} = 0V, I_S = -1A$ |
| DYNAMIC CHARACTERISTICS (Note 8) | | | | | | |
| Input Capacitance | C_{iss} | — | 1614 | — | pF | $V_{DS} = -15V, V_{GS} = 0V$ $f = 1.0\text{MHz}$ |
| Output Capacitance | C_{oss} | — | 226 | — | pF | |
| Reverse Transfer Capacitance | C_{rss} | — | 214 | — | pF | $V_{DS} = 0V, V_{GS} = 0V, f = 1\text{MHz}$ |
| Gate Resistance | R_g | — | 6.8 | — | Ω | |
| Total Gate Charge at 10V | Q_g | — | 35.4 | — | nC | $V_{GS} = -10V, V_{DS} = -15V, I_D = -10A$ |
| Total Gate Charge at 5V | Q_g | — | 18.9 | — | nC | $V_{GS} = -5V, V_{DS} = -15V$ $I_D = -10A$ |
| Gate-Source Charge | Q_{gs} | — | 4.6 | — | nC | |
| Gate-Drain Charge | Q_{gd} | — | 5.7 | — | nC | |
| Turn-On Delay Time | $t_{D(ON)}$ | — | 8.6 | — | ns | $V_{DS} = -15V, V_{GS} = -10V$ $R_L = 1.5\Omega, R_{GEN} = 3\Omega$ |
| Turn-On Rise Time | t_R | — | 12.7 | — | ns | |
| Turn-Off Delay Time | $t_{D(OFF)}$ | — | 44.9 | — | ns | |
| Turn-Off Fall Time | t_F | — | 22.8 | — | ns | |

Notes: 7. Short duration pulse test used to minimize self-heating effect.
8. Guaranteed by design. Not subject to production testing.




Fig. 1 Typical Output Characteristic




Fig. 2 Typical Transfer Characteristic




Fig. 3 Typical On-Resistance vs. Drain Current and Gate Voltage




Fig. 4 Typical On-Resistance vs. Drain Current and Temperature




Fig. 5 On-Resistance Variation with Temperature




Fig. 6 On-Resistance Variation with Temperature




Fig. 7 Gate Threshold Variation vs. Ambient Temperature




Fig. 8 Diode Forward Voltage vs. Current




Fig. 9 Typical Total Capacitance




Fig. 10 Typical Leakage Current vs. Drain-Source Voltage




Fig. 11 Gate Threshold Voltage vs. Total Gate Charge




Fig. 12. SOA, Safe Operation Area





Fig. 13. Transient Thermal Resistance

NOT RECOMMENDED FOR NEW DESIGN

Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

SO-8




| SO-8 | | | |
|----------------------|------|------|------|
| Dim | Min | Max | Typ |
| A | 1.40 | 1.50 | 1.45 |
| A1 | 0.10 | 0.20 | 0.15 |
| b | 0.30 | 0.50 | 0.40 |
| c | 0.15 | 0.25 | 0.20 |
| D | 4.85 | 4.95 | 4.90 |
| E | 5.90 | 6.10 | 6.00 |
| E1 | 3.80 | 3.90 | 3.85 |
| E0 | 3.85 | 3.95 | 3.90 |
| e | -- | -- | 1.27 |
| h | - | -- | 0.35 |
| L | 0.62 | 0.82 | 0.72 |
| Q | 0.60 | 0.70 | 0.65 |
| All Dimensions in mm | | | |

Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

SO-8



| Dimensions | Value (in mm) |
|------------|---------------|
| C | 1.27 |
| X | 0.802 |
| X1 | 4.612 |
| Y | 1.505 |
| Y1 | 6.50 |

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

DIODES is a trademark of Diodes Incorporated in the United States and other countries.
The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
© 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com