

OBSOLETE - PART DISCONTINUED

Product Summary

BV _{bss}	R _{DS(ON)} Max	I _D T _A = +25°C
30V	69mΩ @V _{GS} = 8V	3.2A
	80mΩ @V _{GS} = 4.5V	3.0A

Description

This new generation MOSFET is designed to minimize the footprint in handheld and mobile application. It can be used to replace many small signals MOSFET with as really small footprint.

Applications

- Battery management
- Load switches
- Battery protections
- Handheld and mobile applications


Features and Benefits

- Low Q_g & Q_{gd}
- Small Footprint
- Low Profile 0.30mm Height
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](mailto:contact_us) or your local Diodes representative. <https://www.diodes.com/quality/product-definitions/>**


Mechanical Data

- Package: X2-DSN1006-3
- Terminal Connections: See Diagram Below
- Terminals: Finish – Matte Tin Annealed Over Copper Pillar (e3)

X2-DSN1006-3



Top View



Equivalent Circuit

Ordering Information (Note 4)

Part Number	Package	Packing	
		Qty.	Carrier
DMN3110LCP3-7	X2-DSN1006-3	3,000	Tape & Reel

- Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
 2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
 4. For packaging details, go to our website at <https://www.diodes.com/design/support/packaging/diodes-packaging/>.

Marking Information



C = Product Type Marking Code
 YM = Date Code Marking
 Y or \bar{Y} = Year (ex: J = 2022)
 M or \bar{M} = Month (ex: 9 = September)

Date Code Key

Year	2015	...	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031
Code	C	...	J	K	L	M	N	O	P	R	S	T

Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	O	N	D

Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic			Symbol	Value	Unit
Drain-Source Voltage			V _{DSS}	30	V
Gate-Source Voltage			V _{GSS}	12	V
Continuous Drain Current (Note 5) V _{GS} = 8V	Steady State	T _A = +25°C	I _D	3.2	A
		T _A = +70°C		2.5	
Continuous Drain Current (Note 5) V _{GS} = 4.5V	Steady State	T _A = +25°C	I _D	3.0	A
		T _A = +70°C		2.4	
Pulsed Drain Current (Note 6)			I _{DM}	15	A

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 7)	P _D	0.5	W
Thermal Resistance, Junction to Ambient @T _A = +25°C (Note 7)	R _{θJA}	250	°C/W
Power Dissipation (Note 5)	P _D	1.38	W
Thermal Resistance, Junction to Ambient @T _A = +25°C (Note 5)	R _{θJA}	90	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 8)						
Drain-Source Breakdown Voltage	BV _{DSS}	30	—	—	V	V _{GS} = 0V, I _D = 250μA
Zero Gate Voltage Drain Current T _J = +25°C	I _{DSS}	—	—	100	nA	V _{DS} = 24V, V _{GS} = 0V
Gate-Source Leakage	I _{GSS}	—	—	50	nA	V _{GS} = 10V, V _{DS} = 0V
ON CHARACTERISTICS (Note 8)						
Gate Threshold Voltage	V _{GS(TH)}	0.65	0.8	1.1	V	V _{DS} = V _{GS} , I _D = 250μA
Static Drain-Source On-Resistance	R _{DS(ON)}	—	52	69	mΩ	V _{GS} = 8V, I _D = 0.5A
		—	59	80		V _{GS} = 4.5V, I _D = 0.5A
		—	76	110		V _{GS} = 2.5V, I _D = 0.5A
		—	110	160		V _{GS} = 1.8V, I _D = 0.5A
Forward Transfer Admittance	Y _{fs}	—	3.3	—	S	V _{DS} = 15V, I _D = 0.5A
Diode Forward Voltage	V _{SD}	—	0.7	0.9	V	V _{GS} = 0V, I _S = 0.5A
Reverse Recovery Charge	Q _{RR}	—	1.7	—	nC	V _{DD} = 15V, I _F = 0.5A, di/dt = 300A/μs
Reverse Recovery Time	t _{RR}	—	5.2	—	ns	
DYNAMIC CHARACTERISTICS (Note 9)						
Input Capacitance	C _{iss}	—	110	150	pF	V _{DS} = 15V, V _{GS} = 0V, f = 1MHz
Output Capacitance	C _{oss}	—	71	99		
Reverse Transfer Capacitance	C _{rss}	—	4.3	10		
Series Gate Resistance	R _g	—	21	—	Ω	f = 1MHz, V _{GS} = 0V, V _{DS} = 0V
Total Gate Charge	Q _g	—	1,090	1,520	pC	V _{GS} = 4.5V, V _{DS} = 15V, I _D = 0.5A
Gate-Source Charge	Q _{gs}	—	130	—		
Gate-Drain Charge	Q _{gd}	—	130	—		
Gate Charge at V _{TH}	Q _{g(TH)}	—	110	—		
Turn-On Delay Time	t _{D(ON)}	—	4.8	7	ns	V _{DS} = 15V, V _{GS} = 4.5V, R _g = 2Ω, I _D = 0.5A
Turn-On Rise Time	t _r	—	2.8	—		
Turn-Off Delay Time	t _{D(OFF)}	—	16.5	20		
Turn-Off Fall Time	t _f	—	9.5	—		

- Notes:
- Device mounted on FR-4 material with 1inch² (6.45cm²), 2oz. (0.071mm thick) Cu.
 - Repetitive rating, pulse width limited by junction temperature.
 - Device mounted on FR-4 PCB with minimum recommended pad layout, single sided.
 - Short duration pulse test used to minimize self-heating effect.
 - Guaranteed by design. Not subject to production testing.




Figure 1. Typical Output Characteristic




Figure 2. Typical Transfer Characteristic




Figure 3. Typical On-Resistance vs. Drain Current and Gate Voltage




Figure 4. Typical On-Resistance vs. Drain Current and Junction Temperature




Figure 5. On-Resistance Variation with Junction Temperature




Figure 6. On-Resistance Variation with Junction Temperature




Figure 7. Gate Threshold Variation vs. Junction Temperature




Figure 8. Diode Forward Voltage vs. Current




Figure 9. Typical Junction Capacitance




Figure 10. Gate Charge




Figure 11. SOA, Safe Operation Area




Figure 12. Single Pulse Maximum Power Dissipation

OBSOLETE - PART DISCONTINUED





Figure 13. Transient Thermal Resistance

OBSOLETE

Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

X2-DSN1006-3




X2-DSN1006-3			
Dim	Min	Max	Typ
A	--	0.348	0.32
A1	--	--	0.08
b	0.14	0.16	0.15
b2	0.49	0.51	0.50
D	0.56	0.64	0.60
E	0.96	1.04	1.00
e	--	--	0.35
e1	--	--	0.65
k	--	--	0.325
L	0.21	0.29	0.25
La	0.21	0.29	0.25
All Dimensions in mm			

Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

X2-DSN1006-3



Dimensions	Value (in mm)
G	0.30
G1	0.20
X	0.25
X1	0.70
Y	0.40
Y1	1.10

OBSOLETE - PART DISCONTINUED

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

DIODES is a trademark of Diodes Incorporated in the United States and other countries.
The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
© 2022 Diodes Incorporated. All Rights Reserved.

www.diodes.com