

LT4ME5.0A(CA) - LT4ME200A(CA)

**SURFACE-MOUNT
UNIDIRECTIONAL AND BIDIRECTIONAL
TRANSIENT VOLTAGE SUPPRESSORS**

**STAND-OFF VOLTAGE - 5.0 to 200 Volts
POWER DISSIPATION - 400 Watts**


FEATURES

- For surface-mounted applications
- Reliable low cost construction utilizing molded plastic technique.
- Typical IR less than 1 μ A above 10V
- Fast response time: typically less than 1.0ns for Uni-direction, less than 5.0ns for Bi-direction, from Volts to BV min
- RoHS compliant
- IEC6100-4-2, >30KV(air); >30KV(Contact).(Note 4)
- **Lead-Free Finish; RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](mailto:contact_us) or your local Diodes representative.**
<https://www.diodes.com/quality/product-definitions/>

MECHANICAL DATA

- Package: DO-219AA
- Package Material: "Green" molding compound UL flammability classification 94V-0 (No Br, Sb, Cl) "Halogen-free"
- Moisture Sensitivity: MSL1
- Terminals: Matte Tin $\text{\textcircled{3}}$
- Polarity: by cathode band denotes uni-directional device none cathode band denotes bi-directional device
- Weight: 0.002 ounces, 0.0165 gram (Approximate)

DO-219AA



DO-219AA			
DIM.	MIN.	TYP.	MAX
A	3.5	3.80	3.90
B	1.7	1.90	2.00
C	0.81	1.18	1.20
D	2.70	2.80	2.90
E	0.80	1.00	1.35
F	0.05	0.15	0.30
G	0.35	0.60	0.85
H	0.03	0.07	0.10
I	0°	5°	8°

All Dimensions in millimeter

CATHODE \leftarrow ANODE

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

ABSOLUTE RATINGS

PARAMETER	SYMBOL	VALUE	UNIT
Peak Power Dissipation at TA = 25°C, TP = 1ms (Note 5)	P _{PP}	400	W
Peak Forward Surge Current 8.3ms single half sine-wave @ TJ = 25°C (Note 6)	I _{FSM}	40	A
Steady State Power Dissipation at TL = 120°C	PM(AV)	1.0	W
Maximum Instantaneous forward voltage at 16A for unidirectional devices only (Note 7)	VF	3	V
Operating junction temperature range	T _J	-55 to +175	°C
Storage temperature range	T _{STG}	-55 to +175	°C

Notes:

1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
4. LT4ME5.0 thru LT4ME24 devices that comply IEC 61000-4-2 levels.
5. Non-repetitive current pulse, per fig. 3 and derated above TA = 25°C per fig.1.
6. Only for unidirectional units.
7. VF max = 3V at IF = 16A 300 μ s square wave pulse.

RATING AND CHARACTERISTIC CURVES
LT4ME5.0A(CA) - LT4ME200A(CA)

FIG.1- Pulse Derating Curve




FIG.2- Steady State Power Derating Curve




FIG.3- Pulse Rating Curve




FIG.4- Typical Junction Capacitance





FIG.5- Pulse waveform



Device		Marking code		Reverse stand-off voltage	Breakdown voltage V_{BR} Volts			Maximum reverse voltage at I_{RSM} (clamping)	Maximum reverse surge current	Maximum reverse leakage at V_{RWM}
Uni	Bi	Uni	Bi	V_{RWM} (Volts)	Min.	Max	@ I_T (mA)	V_{RSM} (Volts)	I_{RSM} (Amps)	I_R (μ A)
LT4ME5.0A	LT4ME5.0CA	HE	TE	5.0	6.40	7.07	10	9.2	43.5	800
—	LT4ME6.0CA	—	TG	6.0	6.67	7.37	10	10.3	38.3	800
LT4ME6.5A	LT4ME6.5CA	HK	TK	6.5	7.22	7.98	10	11.2	35.7	500
—	LT4ME8.0CA	—	TR	8.0	8.89	9.83	1	13.6	29.4	50
—	LT4ME8.5CA	—	TT	8.5	9.44	10.43	1	14.4	27.7	10
LT4ME10A	LT4ME10CA	HX	TX	10	11.1	12.3	1	17.0	23.5	5
LT4ME12A	LT4ME12CA	IE	UE	12	13.3	14.7	1	19.9	20.1	0.5
LT4ME14A	LT4ME14CA	IK	UK	14	15.6	17.2	1	23.2	17.2	0.5
LT4ME15A	LT4ME15CA	IM	UM	15	16.7	18.5	1	24.4	16.4	0.5
LT4ME16A	LT4ME16CA	IP	UP	16	17.8	19.7	1	26.0	15.3	0.5
LT4ME17A	—	IR	—	17	18.9	20.9	1	27.6	14.5	0.5
LT4ME18A	—	IT	—	18	20.0	22.1	1	29.2	13.7	0.5
LT4ME20A	—	IV	—	20	22.2	24.5	1	32.4	12.3	0.5
LT4ME22A	LT4ME22CA	IX	UX	22	24.4	27.0	1	35.5	11.2	0.5
LT4ME24A	LT4ME24CA	IZ	UZ	24	26.7	29.5	1	38.9	10.3	0.5
LT4ME26A	LT4ME26CA	JE	VE	26	28.9	31.9	1	42.1	9.5	0.5
LT4ME28A	LT4ME28CA	JG	VG	28	31.1	34.4	1	45.4	8.8	0.5
LT4ME30A	LT4ME30CA	JK	VK	30	33.3	36.8	1	48.4	8.3	0.5
LT4ME33A	LT4ME33CA	JM	VM	33	36.7	40.6	1	53.3	7.5	0.5
LT4ME36A	LT4ME36CA	JP	VP	36	40.0	44.2	1	58.1	6.9	0.5
LT4ME40A	LT4ME40CA	JR	VR	40	44.4	49.1	1	64.5	6.2	0.5
LT4ME43A	—	JT	—	43	47.8	52.8	1	69.4	5.7	0.5
LT4ME45A	—	JV	—	45	50.0	55.3	1	72.7	5.5	0.5
LT4ME48A	LT4ME48CA	JX	VX	48	53.3	58.9	1	77.4	5.2	0.5
LT4ME51A	LT4ME51CA	JZ	VZ	51	56.7	62.7	1	82.4	4.9	0.5
LT4ME54A	—	RE	—	54	60.0	66.3	1	87.1	4.6	0.5
LT4ME58A	LT4ME58CA	RG	WG	58	64.4	71.2	1	93.6	4.3	0.5
LT4ME60A	LT4ME60CA	PK	WK	60	66.7	73.7	1	96.8	4.1	0.5
LT4ME64A	LT4ME64CA	RM	WM	64	71.1	78.6	1	103	3.9	0.5
LT4ME70A	LT4ME70CA	RP	WP	70	77.8	86.0	1	113	3.5	0.5
LT4ME75A	LT4ME75CA	RR	WR	75	83.3	92.1	1	121	3.3	0.5
LT4ME78A	LT4ME78CA	RT	WT	78	86.7	95.8	1	126	3.2	0.5
LT4ME85A	LT4ME85CA	RV	VV	85	94.4	104	1	137	2.9	0.5
LT4ME90A	—	RX	—	90	100	111	1	146	2.7	0.5
LT4ME100A	LT4ME100CA	RZ	WZ	100	111	123	1	162	2.5	0.5
LT4ME110A	—	SE	—	110	122	135	1	177	2.3	0.5
LT4ME120A	—	SG	—	120	133	147	1	193	2.0	0.5
LT4ME150A	—	SM	XM	150	167	185	1	243	1.6	0.5
LT4ME170A	—	SR	—	170	189	209	1	275	1.4	0.5
LT4ME188A	—	SS	—	188	209	231	1	328	1.2	0.5
LT4ME200A	—	ST	—	200	224	248	1	324	1.2	0.5


Notes:

8. Suffix 'A' denotes 5% tolerance device.
9. Add suffix 'C' or 'CA' after part number to specify Bi-directional devices.
10. The IR limit is double for Bi-directional devices.


Ordering Information :

Part Number	Package	Packing	
		Qty.	Carrier
LT4ME _x A(CA) LT4ME _{xx} A(CA) LT4ME _{xxx} A(CA)	DO-219AA	10000pcs	Reel
	DO-219AA	2500pcs	Reel

Marking Information :



Uni-Directional




Bi-Directional

XXXX : Assembly Tracking code
ZZ : Product Type Marking code
Bar Denotes Cathode Side

Packaging Information :

DEVICE	REEL DIA.	Q'TY/REEL	REEL/BOX	Q'TY/BOX	BOX/CARTON	Q'TY/CARTON	BOX SIZE	CARTON SIZE
	(INCH)	(PCS)	(REEL)	(PCS)	(BOX)	(PCS)	(mm)	(mm)
LT4ME _x A(CA) LT4ME _{xx} A(CA) LT4ME _{xxx} A(CA)	13	10000	2	10000	8	160000	334*334*39	350*350*340
	7	2500	4	10000	10	100000	184*184*72	350*350*340

Suggested Pad Layout :



Dimensions	Value (in mm)
C	2.86
G	1.52
X	1.34
X1	4.20
Y	1.80

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.

All other trademarks are the property of their respective owners.

© 2024 Diodes Incorporated. All Rights Reserved.

www.diodes.com