

**SPST Wide Bandwidth Analog Switch****Features**

- CMOS Technology for Bus and Analog Applications
- Low On-Resistance: 8Ω at 3.0V
- Wide V_{CC} Range: 1.65V to 6.0V
- Rail-to-Rail Signal Range
- Control Input Overvoltage Tolerance: 6.0V
- Fast Transition Speed: 2ns at 5.0V
- High Off Isolation: -63dB @ 10MHz
- I/O pins Have Power-off Protection Function
- Break-Before-Make Switching
- Extended Industrial Temperature Range:
-40 °C to 85 °C
- Packaging (Pb-free & Green):
-5-pin SC70


Applications

- Audio, Video Switching, and Routing
- Cell Phones
- PDAs
- Telecommunications
- Portable Instrumentation
- Battery powered Communication Systems
- Computer Peripherals
- Mechanical Relay Replacement

Description

The PI5A121C is a single-pole single throw (SPST) normally open (NO) CMOS switch. The switch is open when IN is LOW. The high-precision device is ideal for low-distortion audio, video, signal switching and routing. Specified over a wide operating power supply voltage, 1.65V to 6.0V, the PI5A121C has on-resistance of 12-ohms at 1.65V, 9-ohms at 2.3V & 6-ohms at 4.5V.

The control input, IN, is independent of supply voltage.

Pin Assignment**Pin Description**

| Pin No | Pin Name | Description |
|--------|----------|-------------------------|
| 1 | COM | Common Output/Data Port |
| 2 | NO | Data Port |
| 3 | GND | Ground |
| 4 | IN | Logic Control |
| 5 | V+ | Positive Power Supply |

Logic Function Table

| Logic Inputs(IN) | Function |
|------------------|----------|
| 0 | OFF |
| 1 | ON |

Maximum Ratings

| | |
|--|--------------------------------|
| Storage Temperature..... | -65 °C to +150 °C |
| Ambient Temperature with Power Applied..... | -40 °C to +85 °C |
| Supply Voltage V ₊ | -0.3V to +7.0V |
| DC Control Voltage V _{IN} | -0.5V to 7.0V |
| DC Input Voltage (V _{NO} , V _{COM})..... | -0.3V to V ₊ + 0.5V |
| DC Output Current I _{OUT} | 128mA |
| DC V ₊ or Ground Current I ₊ /I _{GND} | ±100mA |
| Junction Temperature under Bias (T _J) | 150 °C |
| Junction Lead Temperature (T _L) (Soldering, 10 seconds) | 260 °C |
| Power Dissipation (P _D) @ +85 °C | 180mW |
| ESD (HBM)..... | 2000V |

Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

Recommended Operating Conditions

| Symbol | Parameter | Conditions | Min. | Typ. | Max. | Unit |
|---------------------------------|----------------------------------|-------------------------------|------|------|----------------|------|
| V ₊ | Operating Voltage | - | 1.65 | - | 6.0 | V |
| V _{IN} | Control Input Voltage | - | 0 | - | 6.0 | V |
| V _{INPUT} | Switch Input Voltage | - | 0 | - | V ₊ | V |
| V _{OUT} | Output Voltage | - | 0 | - | V ₊ | V |
| T _A | Operating Temperature | - | -40 | 25 | 85 | °C |
| t _r , t _f | Control Input Rise and Fall Time | V ₊ = 2.3V to 3.6V | 0 | - | 10 | ns/V |
| | | V ₊ = 4.5V to 6.0V | 0 | - | 5 | ns/V |

Note: Control input must be held HIGH or LOW; it must not float.

DC Electrical Characteristics

($T_A = -40^\circ\text{C}$ to 85°C , unless otherwise noted.)

| Parameter | Description | Test Conditions | Temperature | Min | Typ | Max | Units |
|--------------|--|--|-----------------|-----|-----|-----------|---------------|
| V_{IAR} | Analog Input Signal Range | V_+ | -40 °C to 85 °C | 0 | - | 6 | V |
| R_{ON} | ON Resistance ⁽¹⁾ | $V_+=4.5\text{V}, I_O=30\text{mA}, V_{INPUT}=0\text{V}$ | 25 °C | - | 4 | 6 | Ω |
| | | $V_+=4.5\text{V}, I_O=-30\text{mA}, V_{INPUT}=2.4\text{V}$ | | - | 5 | 8 | |
| | | $V_+=4.5\text{V}, I_O=-30\text{mA}, V_{INPUT}=-4.5\text{V}$ | | - | 7 | 11 | |
| | | $V_+=4.5\text{V}, I_O=30\text{mA}, V_{INPUT}=0\text{V}$ | -40 °C to 85 °C | - | - | 6 | |
| | | $V_+=4.5\text{V}, I_O=-30\text{mA}, V_{INPUT}=2.4\text{V}$ | | - | - | 8 | |
| | | $V_+=4.5\text{V}, I_O=-30\text{mA}, V_{INPUT}=-4.5\text{V}$ | | - | - | 11 | |
| | | $V_+=3.0\text{V}, I_O=24\text{mA}, V_{INPUT}=0\text{V}$ | 25 °C | - | 5 | 8 | |
| | | $V_+=3.0\text{V}, I_O=-24\text{mA}, V_{INPUT}=-3.0\text{V}$ | | - | 10 | 15 | |
| | | $V_+=3.0\text{V}, I_O=24\text{mA}, V_{INPUT}=0\text{V}$ | -40 °C to 85 °C | - | - | 8 | |
| | | $V_+=3.0\text{V}, I_O=-24\text{mA}, V_{INPUT}=3.0\text{V}$ | | - | - | 15 | |
| | | $V_+=2.3\text{V}, I_O=8\text{mA}, V_{INPUT}=0\text{V}$ | 25 °C | - | 6 | 9 | |
| | | $V_+=2.3\text{V}, I_O=-8\text{mA}, V_{INPUT}=2.3\text{V}$ | | - | 13 | 20 | |
| | | $V_+=2.3\text{V}, I_O=8\text{mA}, V_{INPUT}=0\text{V}$ | -40 °C to 85 °C | - | - | 9 | |
| | | $V_+=2.3\text{V}, I_O=-8\text{mA}, V_{INPUT}=2.3\text{V}$ | | - | - | 20 | |
| | | $V_+=1.65\text{V}, I_O=4\text{mA}, V_{INPUT}=0\text{V}$ | 25 °C | - | 8 | 12 | |
| | | $V_+=1.65\text{V}, I_O=-4\text{mA}, V_{INPUT}=1.65\text{V}$ | | - | 20 | 30 | |
| | | $V_+=1.65\text{V}, I_O=4\text{mA}, V_{INPUT}=0\text{V}$ | -40 °C to 85 °C | - | - | 12 | |
| | | $V_+=1.65\text{V}, I_O=-4\text{mA}, V_{INPUT}=1.65\text{V}$ | | - | - | 30 | |
| R_{ONF} | ON Resistance ^(1,2,3) Flatness | $V_+=5.0\text{V}, I_A=-30\text{mA}, 0 \leq V_{INPUT} \leq V_+$ | 25 °C | - | 6 | - | Ω |
| | | $V_+=3.3\text{V}, I_A=-24\text{mA}, 0 \leq V_{INPUT} \leq V_+$ | | - | 12 | - | |
| | | $V_+=2.5\text{V}, I_A=-8\text{mA}, 0 \leq V_{INPUT} \leq V_+$ | | - | 22 | - | |
| | | $V_+=1.8\text{V}, I_A=-4\text{mA}, 0 \leq V_{INPUT} \leq V_+$ | | - | 90 | - | |
| V_{IH} | Input High Voltage (Logic High Level) | $V_+=1.65\text{V}$ | -40 °C to 85 °C | 1 | - | - | V |
| | | $V_+=2.3\text{V}$ | | 1.2 | - | - | |
| | | $V_+=3\text{V}$ | | 1.3 | - | - | |
| | | $V_+=4.2\text{V}$ | | 1.5 | - | - | |
| | | $V_+=6.0\text{V}$ | | 1.8 | - | - | |
| V_{IL} | Input Low Voltage (Logic Low Level) | $V_+=1.65\text{V}$ | -40 °C to 85 °C | - | - | 0.4 | V |
| | | $V_+=2.3\text{V}$ | | - | - | 0.6 | |
| | | $V_+=3\text{V}$ | | - | - | 0.8 | |
| | | $V_+=4.2\text{V}$ | | - | - | 1 | |
| | | $V_+=6.0\text{V}$ | | - | - | 1.2 | |
| I_{LKC} | Logic Input Leakage Current | $0 \leq V_{IN} \leq 6.0\text{V}, V_+=0\text{V}$ to 6.0V | 25 °C | - | - | ± 0.1 | μA |
| | | | -40 °C to 85 °C | - | - | ± 1.0 | |
| I_{OFF} | OFF State Leakage Current | $0 \leq V_{INPUT} \leq V_+, V_+=1.65\text{V}$ to 6.0V | 25 °C | - | - | ± 0.1 | μA |
| | | | -40 °C to 85 °C | - | - | ± 10 | |
| I_{PWROFF} | Input Leakage Current for Power off | $0 \leq V_{INPUT} \leq 6.0\text{V}, V_+=0\text{V}$ | 25 °C | - | - | ± 1 | μA |
| | | | -40 °C to 85 °C | - | - | ± 5 | |
| I_+ | Quiescent Supply Current | All channels ON or OFF, $V_{IN} = V_+$ or GND, $I_{OUT}=0$, $V_+=6.0\text{V}$ | 25 °C | - | - | 1 | μA |
| | | | -40 °C to 85 °C | - | - | 5 | |

Notes:

- Measured by voltage drop between COM and NO pins at the indicated current through the device. ON resistance is determined by the lower of the voltages on two ports (COM or NO).
- Parameter is characterized but not tested in production.
- Flatness is defined as difference between maximum and minimum value of ON resistance over the specified range of conditions. Guaranteed by design.

Capacitance⁽¹⁾

(T_A = 25 °C, unless otherwise noted.)

| Symbol | Parameter | Test Conditions | Min. | Typ. | Max. | Units |
|---------------------|---------------------|---|------|------|------|-------|
| C _{IN} | Control Input | V ₊ = 5.0V, f = 1 MHz ⁽¹⁾ | - | 2.5 | - | pF |
| C _{OFF} | NO Port, Switch OFF | | - | 5.0 | - | |
| C _{COM ON} | COM Port, Switch ON | | - | 15.0 | - | |

Notes:




1. Capacitance is characterized but not tested in production

Switch and AC Characteristics⁽¹⁾

| Parameter | Description | Test Conditions | Supply Voltage | Temperature | Min | Typ | Max | Units |
|------------------|------------------|---|---|-------------|-----|-----|-----|-------|
| t _{ON} | Turn-On Time | R _L =100Ω, C _L =35pF, See Test Circuit Figure 1. | V ₊ = 3.3V, V _{NO} =3.0V, V _{IH} =3.0V, | -40~+85 °C | - | 3.6 | 6 | |
| | | | V ₊ = 5.0V, V _{NO} =3V, V _{IL} =3V, | | - | 3 | 5 | |
| t _{OFF} | Turn-Off Time | R _L =100Ω, C _L =35pF, See Test Circuit Figure 1. | V ₊ = 3.3V, V _{NO} =3.0V, V _{IH} =3.0V, | -40~+85 °C | - | 3 | 5 | ns |
| | | | V ₊ = 5.0V, V _{NO} =3V, V _{IL} =3V, | | - | 2.5 | 4 | |
| Q | Charge Injection | C _L = 1nF, V _{GEN} = 0V, R _{GEN} =0Ω. See Test Circuit Figure 2. | V ₊ = 5.0V | +25 °C | - | 5 | - | pC |
| | | | V ₊ = 3.3V | | - | 4 | - | |
| OIRR | Off Isolation | R _L =50Ω, V _{GEN} =0V, R _{GEN} =0Ω, f=10MHz. | V ₊ = 1.65V to 5.5V | 25 °C | - | -63 | - | db |
| f _{3dB} | -3dB Bandwidth | See Test Circuit Figure 5. | V ₊ = 1.65V to 5.5V | +25 °C | - | 500 | - | MHz |

Notes:

1. Guaranteed by design.

Test Circuits and Timing Diagrams

Figure 1. Switching Time

Figure 2. Charge Injection

Figure 3. Channel-Off Capacitance




Figure 4. Channel-On Capacitance





Figure 5. Bandwidth

Mechanical Information

5-pin SC70 (C)



Ordering Information

| Part Number | Package Code | Package | Top Marking |
|-------------|--------------|--------------------------------|-------------|
| PI5A121CCE | C | Lead Free and Green SC70-5 (C) | rD |

Notes:

- E = Pb-free and Green
- Adding X Suffix= Tape/Reel

Pericom Semiconductor Corporation • 1-800-435-2336 • www.pericom.com

Pericom reserves the right to make changes to its products or specifications at any time, without notice, in order to improve design or performance and to supply the best possible product. Pericom does not assume any responsibility for use of any circuitry described other than the circuitry embodied in Pericom product. The company makes no representations that circuitry described herein is free from patent infringement or other rights, of Pericom.