

Features

- Schottky Barrier Chip
- Guard Ring Die Construction for Transient Protection
- Low Power Loss, High Efficiency
- High Surge Capability
- High Current Capability and Low Forward Voltage Drop
- Surge Overload Rating to 40A Peak
- For Use in Low Voltage, High Frequency Inverters, Free Wheeling, and Polarity Protection Applications
- **Lead-Free Finish; RoHS Compliant (Notes 1 & 2)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](#) or your local Diodes representative. <https://www.diodes.com/quality/product-definitions/>**

Mechanical Data

- Case: DO-41
- Case Material: Molded Plastic. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020C
- Terminals: Finish – Bright Tin. Plated Leads Solderable per MIL-STD-202, Method 208
- Polarity: Cathode Band
- Mounting Position: Any
- Marking: Type Number
- Weight: 0.3 grams (Approximate)

Ordering Information (Note 3)

Device	Packaging	Shipping
SB120-A	DO-41 (Plastic)	5K/Ammo Pack
SB120-B	DO-41 (Plastic)	1K/Bulk
SB120-T (Note 4)	DO-41 (Plastic)	5K/Tape & Reel, 13-inch
SB130-A	DO-41 (Plastic)	5K/Ammo Pack
SB130-B (Note 4)	DO-41 (Plastic)	1K/Bulk
SB130-T	DO-41 (Plastic)	5K/Tape & Reel, 13-inch
SB140-A	DO-41 (Plastic)	5K/Ammo Pack
SB140-B	DO-41 (Plastic)	1K/Bulk
SB140-T	DO-41 (Plastic)	5K/Tape & Reel, 13-inch
SB150-A	DO-41 (Plastic)	5K/Ammo Pack
SB150-B	DO-41 (Plastic)	1K/Bulk
SB150-T	DO-41 (Plastic)	5K/Tape & Reel, 13-inch
SB160-A	DO-41 (Plastic)	5K/Ammo Pack
SB160-B	DO-41 (Plastic)	1K/Bulk
SB160-T	DO-41 (Plastic)	5K/Tape & Reel, 13-inch

- Notes:
1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
 2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
 3. For packaging details, visit our website at <https://www.diodes.com/design/support/packaging/diodes-packaging/>.
 4. Not recommended for new design.

Maximum Ratings and Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

Characteristic	Symbol	SB120	SB130	SB140	SB150	SB160	Unit
Peak Repetitive Reverse Voltage	V _{RRM}	20	30	40	50	60	V
Working Peak Reverse Voltage	V _{RWM}						
DC Blocking Voltage	V _R						
RMS Reverse Voltage	V _{R(RMS)}	14	21	28	35	42	V
Average Rectified Output Current (Note 5) (See Figure 1)	I _O	1.0					A
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load (JEDEC Method)	I _{FSM}	40					A
Forward Voltage (Note 6) @ I _F = 1.0A	V _{FM}	0.50		0.70			V
Peak Reverse Current @ T _A = +25°C at Rated DC Blocking Voltage (Note 6) @ T _A = +100°C	I _{RM}	0.5			5.0		mA
Typical Thermal Resistance Junction to Lead (Note 5)	R _{θJL}	15					°C/W
Typical Thermal Resistance Junction to Ambient	R _{θJA}	50					°C/W
Operating Temperature Range	T _J	-65 to +125			-65 to +150		°C
Storage Temperature Range	T _{STG}	-65 to +150					

Notes: 5. Measured at ambient temperature at a distance of 9.5mm from the case.
6. Short duration pulse test used to minimize self-heating effect.




Fig. 1 Forward Current Derating Curve




Fig. 2 Typical Forward Characteristics - SB120 thru SB140




Fig. 3 Typical Forward Characteristics - SB150 thru SB160




Fig. 4 Max Non-Repetitive Peak Fwd Surge Current




Fig. 5 Typical Total Capacitance




Fig. 6 Typical Reverse Characteristics, SB120 thru SB140





Fig. 7 Typical Reverse Characteristics, SB150 thru SB160

Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

DO-41 (Plastic)



DO-41 (Plastic)		
Dim	Min	Max
A	25.40	-
B	4.06	5.21
C	0.71	0.864
D	2.00	2.72
All Dimensions in mm		

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2019, Diodes Incorporated

www.diodes.com