


**Features**

- ➔ Factory-Set Reset Threshold Voltages for Nominal Supplies from 1.2V to 1.8V
- ➔ Low power consumption : Typ 7.5µA
- ➔ Five different timeout periods available: 70µs(voltage detector), 1.5ms, 30ms, 210ms and 1.68s
- ➔ Output configuration: Push-pull  $\overline{\text{RESET}}$ , push-pull RESET or open-drain RESET
- ➔ Guaranteed reset valid to Vcc: 0.9V--active low, 0.85V--active high
- ➔ Detect voltage accuracy: ±1.5%
- ➔ Adjustable threshold reset-in option
- ➔ Immune to short negative Vcc transients
- ➔ Small SOT23-3L, SC70-3L or SOT143-4L packages

**Pin Configuration**



**Description**

The PT7M6832–6840 are microprocessor (µP) supervisory circuits used to monitor low-voltage power supplies in µP and digital systems. They provide excellent circuit reliability and low cost by eliminating external components and adjustments when used with +1.2V to +1.8V powered circuits.

These devices assert a reset signal whenever the VCC supply voltage declines below a preset threshold or whenever manual reset ( $\overline{\text{MR}}$ ) is asserted. Reset remains asserted for a fixed timeout delay after VCC has risen above the reset threshold or when manual reset is deasserted. Five different timeout periods are available: 70µs (voltage detector), 1.5ms, 30ms, 210ms, and 1.68s. Reset thresholds suitable for operation with a variety of supply voltages are available.

The PT7M6832/PT7M6835/PT7M6838 have a push-pull active-low reset output ( $\overline{\text{RESET}}$ ). The PT7M6833/PT7M6836/PT7M6839 have a push-pull active-high reset output (RESET) and the PT7M 6834/ PT7M 6837/ PT7M 6840 have an open-drain active-low reset output ( $\overline{\text{RESET}}$ ). The open-drain active-low reset output requires a pull-up resistor that can be connected to a voltage higher than VCC.

The PT7M6835/PT7M6836/PT7M6837 feature a debounced manual reset input ( $\overline{\text{MR}}$ ), while the PT7M6838/PT7M6839/PT7M6840 provide a RESET-IN input allowing the user to externally adjust the reset threshold. The reset comparator is designed to ignore fast transients on VCC.

Low supply current of 7.5µA makes the PT7M6832–PT7M6840 ideal for use in portable equipment. These devices are available in 3-pin SOT23 or 4-pin SOT143 packages.

**Applications**

- ➔ Computers
- ➔ Controllers
- ➔ Intelligent Instruments
- ➔ Critical µP and µC Power Monitoring
- ➔ Portable/Battery-Powered Equipment

## Pin Description


### PT7M6832- PT7M6837

PT7M6833 SOT23-3 SC70-3	PT7M6832/ PT7M6834 SOT23-3 SC70-3	PT7M6836	PT7M6835/ PT7M6837	Name	Description
1	1	1	1	GND	Ground
-	2	-	4	$\overline{\text{RESET}}$	Reset Output, Open-Drain or Push-Pull, Active-Low. /RESET changes from HIGH to LOW when Vcc drops below the selected reset threshold or /MR is pulled low. /RESET remains LOW for the reset timeout period after Vcc exceeds the device reset threshold and /MR is released high.
2	-	4	-	RESET	Reset Output, Push-Pull, Active-High. RESET changes from LOW to HIGH when the Vcc input drops below the selected reset threshold or /MR is pulled low. RESET remains HIGH for the reset timeout period after Vcc exceeds the device reset threshold and /MR is released high.
-	-	3	3	$\overline{\text{MR}}$	Active-Low Manual Reset Input. Internal 20kΩ pull-up to Vcc. Pull LOW to force a reset. Reset remains active as long as MR is LOW and for the reset timeout period after MR goes HIGH. Leave unconnected or connect to Vcc if unused
3	3	2	2	VCC	Supply Voltage and Monitored Supply


### PT7M6838- PT7M6840

PT7M6839	PT7M6838/ PT7M6840	Name	Description
3	3	RESET-IN	Adjustable Reset Threshold Input. High-impedance input for reset comparator. Connect this pin to an external resistive-divider network to set the reset threshold voltage; the typical threshold is 0.44V. Reset is asserted when RESET-IN is below the threshold (VCC is not monitored).
2	2	Vcc	Supply Voltage (1.3V to 5.5V)
1	1	GND	Ground
4	-	RESET	Reset Output, Push-Pull, Active-High. RESET changes from LOW to HIGH when the RESET-IN input drops below the typical reset threshold (0.44V). RESET remains HIGH for the reset timeout period after RESET-IN exceeds the reset threshold.
-	4	$\overline{\text{RESET}}$	Reset Output, Open-Drain or Push-Pull, Active-Low. /RESET changes from HIGH to LOW when RESET-IN drops below the typical reset threshold (0.44V). /RESET remains LOW for the reset timeout period after RESET-IN exceeds the reset threshold.

**Block Diagram**



**Fig.1** PT7M6832-PT7M6837 Block Diagram



**Fig.2** PT7M6838-PT7M6840 Block Diagram

## Maximum Ratings

Storage Temperature.....	- 65°C to +150°C
Ambient Temperature with Power Applied.....	-40°C to +85°C
Supply Voltage to Ground Potential (V <sub>CC</sub> to GND).....	- 0.3V to +6.0V
Open-drain RESET, MR.....	- 0.3V to +6.0V
RESET-IN, Push-pull RESET and RESET.....	-0.3V to +6.0V
DC Input/Output Current .....	20mA
Power Dissipation.....	245mW

### Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

## AC Electrical Characteristics

(V<sub>CC</sub> = +0.9V to +5.5V, unless otherwise noted. Typical values are at T<sub>A</sub> = +25°C)

Description	Symbol	Test Conditions	Min	Typ	Max	Unit
Reset Active Timeout Period	t <sub>PD</sub>	D0	-	0.07	-	ms
		D1	1	1.5	2	
		D2	20	30	40	
		D3	140	210	280	
		D4	1120	1680	2240	
V <sub>CC</sub> or RESET-IN to Reset Delay		V <sub>CC</sub> falling, step signal from (V <sub>TH</sub> +100mV) to (V <sub>TH</sub> -100mV)	-	60	-	μs
Propagation Delay(D0 only)	t <sub>P</sub>	V <sub>CC</sub> rising, step signal from (V <sub>TH</sub> -100mV) to (V <sub>TH</sub> +100mV)	-	70	-	μs
Startup Time(D0 only)	-	V <sub>CC</sub> rising from 0 to 1.1V(t <sub>R</sub> < 1μs)	-	150	-	μs
$\overline{\text{MR}}$ Minimum Input Pulse Width	-	$\overline{\text{MR}}$ driven from V <sub>CC</sub> to 0	2	-	-	μs
$\overline{\text{MR}}$ Glitch Rejection	-	$\overline{\text{MR}}$ driven from V <sub>CC</sub> to 0	-	100	-	ns
$\overline{\text{MR}}$ to Reset Delay	-	$\overline{\text{MR}}$ driven from V <sub>CC</sub> to 0	-	500	-	ns

**DC Electrical Characteristics**

 ( $V_{CC} = +0.9V$  to  $+5.5V$ , unless otherwise noted. Typical values are at  $T_A = +25^\circ C$ )

Description	Sym.	Test Conditions	Min	Typ	Max	Unit
Operating Voltage Range	$V_{CC}$	$T_A = -40^\circ C \sim +85^\circ C$ , PT7M6832/6835/6838, PT7M6834/6837/6840	0.9	-	5.5	V
		$T_A = -40^\circ C \sim +85^\circ C$ , PT7M6833/6836/6839	0.85	-	5.5	
		$T_A = 0^\circ C \sim +85^\circ C$ , PT7M6833/6836/6839	0.75	-	5.5	
		$T_A = -40^\circ C \sim +85^\circ C$ , PT7M6838/6839/6840	1.5	-	5.5	
Supply Current	$I_{CC}$	$V_{CC} = 1.2V$ , no load, reset not asserted	-	7.5	13	$\mu A$
		$V_{CC} = 1.8V$ , no load, reset not asserted	-	9	16	
		$V_{CC} = 3.6V$ , no load, reset not asserted	-	16	25	
Reset Threshold	$V_{TH}$	W	1.620	1.665	1.710	V
		V	1.530	1.575	1.620	
		I	1.350	1.388	1.425	
		H ( $-10^\circ C \sim +85^\circ C$ )	1.275	1.313	1.350	
		G ( $0^\circ C \sim +85^\circ C$ )	1.080	1.110	1.140	
		F* ( $0^\circ C \sim +85^\circ C$ )	1.020	1.050	1.080	
RESET-IN Threshold	$V_{RSTIN}$	$1.5V \leq V_{CC} \leq 5.5V$ , RESET-IN falling from high to low ( $25^\circ C$ )	-2%	444	+2%	
		$1.5V \leq V_{CC} \leq 5.5V$ , RESET-IN rising from low to high ( $0^\circ C \sim 85^\circ C$ )	-5%	444	+5%	
Reference voltage temperature coefficient	$T_C$	Reference voltage temperature coefficient, $-40^\circ C \sim +85^\circ C$	-	70	-	ppm/ $^\circ C$
Push-pull $\overline{RESET}$ Output High Voltage	$V_{OH}$	$V_{CC} \geq 1.1V$ , $I_{source} = 50\mu A$ , reset not asserted	$0.8 \times V_{CC}$	-	-	-
		$V_{CC} \geq 1.5V$ , $I_{source} = 150\mu A$ , reset not asserted	$0.8 \times V_{CC}$	-	-	
		$V_{CC} \geq 1.0V$ , $I_{source} = 50\mu A$ , reset asserted	$0.8 \times V_{CC}$	-	-	
		$V_{CC} \geq 1.5V$ , $I_{source} = 150\mu A$ , reset asserted	$0.8 \times V_{CC}$	-	-	
Push-pull $\overline{RESET}$ Output Low Voltage	$V_{OL}$	$V_{CC} \geq 1.0V$ , $I_{sink} = 80\mu A$ , reset asserted	-	-	$0.2 \times V_{CC}$	V
		$V_{CC} \geq 1.5V$ , $I_{sink} = 200\mu A$ , reset asserted	-	-	$0.2 \times V_{CC}$	
Push-pull $\overline{RESET}$ Output Low Voltage		$V_{CC} \geq 1.1V$ , $I_{sink} = 80\mu A$ , reset not asserted	-	-	$0.2 \times V_{CC}$	
		$V_{CC} \geq 1.5V$ , $I_{sink} = 200\mu A$ , reset not asserted	-	-	$0.2 \times V_{CC}$	
Open-Drain $\overline{RESET}$ Output Low Voltage		$V_{CC} \geq 1.0V$ , $I_{sink} = 80\mu A$ , reset asserted	-	-	0.15	V
		$V_{CC} \geq 1.5V$ , $I_{sink} = 200\mu A$ , reset asserted	-	-	0.2	
$\overline{MR}$ Input Voltage	$V_{IL}$	-	-	-	$0.3 \times V_{CC}$	V
	$V_{IH}$	-	$0.7 \times V_{CC}$	-	-	
Open-Drain $\overline{RESET}$ Output Leakage Current	$I_{LKG}$	$V_{CC} > V_{TH}$ , reset not asserted	-	-	1.0	$\mu A$
RESET-IN Leakage Current	$I_{RSTIN}$	-	-25	-	+25	nA
Reset Threshold Hysteresis	$V_{HYS}$	-	-	0.75	-	% $V_{TH}$

## Functional Description

### Reset Output

The PT7M6832-PT7M6840 assert a reset to prevent code-execution errors during power-up, power-down, or brownout conditions. They also assert a reset signal whenever the V<sub>CC</sub> supply voltage falls below a preset threshold (PT7M6832-PT7M6837) or RESET-IN falls below the adjustable threshold (PT7M6838-PT7M6840), keeping reset asserted for a fixed timeout delay (Table 2) after V<sub>CC</sub> or RESET-IN has risen above the reset threshold. The PT7M6832/6835/6838 use a push-pull active-low output, the PT7M6833/6836/6839 have a push-pull active-high output, and the PT7M6834/6837/ 6840 have an open-drain active-low output stage. Connect a pull-up resistor on the PT7M6834/6837/ 6840's RESET output to any supply between 0 and 6V.

### Manual Reset Input


Reset remains asserted while  $\overline{MR}$  is low, and for a fixed timeout delay after  $\overline{MR}$  returns high. This input has an

internal 20k $\Omega$  pull-up resistor, so it can be left open if it is not used.  $\overline{MR}$  can be driven with CMOS logic level, or with open-drain/collector outputs. To create a manual reset function, connect a normally open momentary switch from  $\overline{MR}$  to ground; external debounce circuitry is not required.

### RESET-IN

The PT7M6838/6839/6840 features a RESET-IN input for monitoring supply voltages down to 0.44V. An external resistive-divider network can be used to set voltage monitoring thresholds as shown in Fig.3. As the monitored voltage falls, the voltage at RESET-IN decreases and asserts a reset when it falls below the RESET-IN threshold (V<sub>RSTIN</sub>). The low-leakage current at RESET-IN allows for relatively large-value resistors to be used, which reduce power consumption. For example, for a 0.6V monitored trip level, if R<sub>2</sub> = 200k $\Omega$ , then R<sub>1</sub> = 70.3k $\Omega$ .

**Note:** The minimum V<sub>CC</sub> of 1.3V is required to guarantee the RESET-IN threshold accuracy.



**Fig.3** External setting of adjustable threshold

## Application Information

### Negative-Going VCC Transients

In addition to issuing a reset to the  $\mu\text{P}$  during power-up, power-down, and brownout conditions, the PT7M6832–PT7M6840 are relatively immune to short-duration negative-going Vcc transients. A  $0.1\mu\text{F}$  bypass capacitor mounted as close as possible to the Vcc pin provides additional transient immunity.

### Valid Reset Output Down to Vcc = 0

When Vcc falls below 0.9V, the PT7M6832/6835/6838 push-pull RESET output no longer sinks current for it becomes an open circuit. Therefore, high-impedance CMOS logic inputs connected to RESET can drift to undetermined voltages. This presents no problem in most applications since most  $\mu\text{P}$  and other circuitry are inoperative with Vcc lower than 0.9V. However, in applications where RESET must be valid down to 0, adding a pull-down resistor to RESET causes any stray leakage currents to flow to ground, holding RESET low (Fig.4). R3's value is not critical;  $100\text{k}\Omega$  is large enough not to load RESET and small enough to pull RESET to ground.




Fig.4 Reset output valid to VCC=0 circuit

A  $100\text{k}\Omega$  pull-up resistor to Vcc is also recommended for the PT7M6833/PT7M6836/PT7M6839 if RESET is required to remain valid for  $V_{cc} < 0.85\text{V}$ .

### Interfacing to $\mu\text{Ps}$ with Bidirectional Reset Pins

Since the RESET output on the PT7M6834/6837/6840 is open-drain, these devices interface easily with  $\mu\text{Ps}$  that have bidirectional reset pins. Connecting the  $\mu\text{P}$  supervisor's RESET output directly to the  $\mu\text{P}$ 's RESET pin with a single pull-up resistor allows either device to assert a reset (Fig.5).

### Open-Drain RESET Output with Multiple Supplies

In some systems the open-drain output is used to level-shift from the monitored supply to reset circuitry powered by some other supply (Fig.6).

**Note:** As the PT7M6834/6837/6840's Vcc decreases, so does the IC's ability to sink current at RESET. Also, with any pull-up, RESET will be pulled high as Vcc declines toward 0. The voltage where this occurs depends on the pull-up resistor value and the voltage to which it is connected.




Fig.5 Interfacing to  $\mu\text{Ps}$  with Bidirectional Reset I/O





Fig.6 Open-drain Reset output with multiple supplies

**Application Circuit**





**Part Marking**

Top mark not available at this time. To obtain advance information regarding the top mark, please contact your local sales representative.



**Packaging Mechanical**

**4-SOT143 (TB)**



PKG. DIMENSIONS(MM)		
SYMBOL	Min	Max
A	0.80	1.22
A1	0.00	0.15
A2	0.75	1.07
b	0.30	0.50
b1	0.75	0.90
c	0.08	0.20
D	2.80	3.04
d	0.20 BSC	
E	1.20	1.40
E1	2.10	2.64
e	1.92 BSC	
L	0.30	0.60
θ	0°	8°

**Note:**

1. Comply with TO-253D/AA except A1 Min, b1 Min, b1 Max, and L Min.
2. PACKAGE OUTLINE DIMENSIONS DO NOT INCLUDE MOLD FLASH AND METAL BURR

		DATE: 03/29/16
DESCRIPTION: 4-Pin, SOT143		
PACKAGE CODE: TB (TB4)		
DOCUMENT CONTROL#: PD-2146		REVISION: A

16-0083

**3-SOT23 (TA)**



PKG. DIMENSIONS(MM)		
SYMBOL	Min	Max
A	-	1.45
A1	0.00	0.15
A2	0.90	1.30
b	0.30	0.50
c	0.08	0.22
D	2.75	3.10
E	1.45	1.75
E1	2.60	3.00
e	0.95 BSC	
e1	1.90 BSC	
L	0.30	0.60
θ	0°	8°

**Note:**  
1. Comply with MO-178C, except D Max.  
2. PACKAGE OUTLINE DIMENSIONS DO NOT INCLUDE MOLD FLASH AND METAL BURR

		DATE: 03/29/16
DESCRIPTION: 3-Pin, Small Outline Transistor Plastic Package (SOT23)		
PACKAGE CODE: TA (TA3)		
DOCUMENT CONTROL #: PD-2143	REVISION: A	

16-0080

3-SC70 (C)



PKG. DIMENSIONS(MM)		
SYMBOL	Min	Max
A	-	1.10
A1	0.00	0.10
A2	0.70	1.00
b	0.15	0.40
c	0.08	0.22
D	1.80	2.20
E	1.10	1.40
E1	1.75	2.45
e	0.65 BSC	
e1	1.30 BSC	
L	0.26	0.46
$\theta$	0°	8°

Note:

1. Comply with MO-203C, except b Max, D Min, D Max, E1 Min and E1 Max.
2. PACKAGE OUTLINE DIMENSIONS DO NOT INCLUDE MOLD FLASH AND METAL BURR



DATE: 03/29/16

DESCRIPTION: 3-Pin, SOT323 (SC70)

PACKAGE CODE: C (C3)

DOCUMENT CONTROL#: PD-2147

REVISION: A

16-0077

For latest package info.

please check: <http://www.diodes.com/design/support/packaging/pericom-packaging/packaging-mechanicals-and-thermal-characteristics/>

## Ordering Information

Part Number	Package Code	Package
PT7M6832xDxTA3EX	TA	3-Pin, Small Outline Transistor Plastic Package (SOT23)
PT7M6832xDxC3EX	C	3-Pin, SOT323 (SC70)
PT7M6833xDxTA3EX	TA	3-Pin, Small Outline Transistor Plastic Package (SOT23)
PT7M6833xDxC3EX	C	3-Pin, SOT323 (SC70)
PT7M6834xDxTA3EX	TA	3-Pin, Small Outline Transistor Plastic Package (SOT23)
PT7M6834xDxC3EX	C	3-Pin, SOT323 (SC70)
PT7M6835xDxTBEX	TB	4-Pin (SOT143)
PT7M6836xDxTBEX	TB	4-Pin (SOT143)
PT7M6837xDxTBEX	TB	4-Pin (SOT143)
PT7M6838DxTBEX	TB	4-Pin (SOT143)
PT7M6839DxTBEX	TB	4-Pin (SOT143)
PT7M6840DxTBEX	TB	4-Pin (SOT143)

### Notes:

- EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- See <http://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- Thermal characteristics can be found on the company web site at [www.diodes.com/design/support/packaging/](http://www.diodes.com/design/support/packaging/)
- E = Pb-free and Green
- X suffix = Tape/Reel

**Table 1** Suffix "x" definition of Threshold

Suffix	Reset Threshold(V)
W	1.665
V	1.575
I	1.388
H	1.313
G	1.110
F	1.050

**Table 2** Suffix "Dx" definition of Timeout Period

Suffix	Reset Active Timeout Period(ms)
D0	0.07
D1	1.5
D2	30
D3	210
D4	1680

## Function comparison of PT7M6832- PT7M6840

Item	Part No.	Output Open-Drain		Output Push-Pull	
		Active high	Active low	Active high	Active low
1	PT7M6832/6835/6838	-	-	-	√
2	PT7M6833/6836/6839	-	-	√	-
3	PT7M6834/6837/6840	-	√	-	-

**IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

**LIFE SUPPORT**

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.