# THE ULN2003V12, ULN2003F12 ARE <u>NOT</u> RECOMMENDED FOR NEW DESIGNS. PLEASE <u>CONTACT US</u>.

## ULN2003V12, ULN2003F12



### MULTI CHANNEL RELAY AND INDUCTIVE LOAD SINK DRIVER

## **Description**

The ULN2003V12 and ULN2003F12 are multi-channel sink drivers comprised of 7-channel and 4-channel output stages respectively. The ULN2003V12 sink driver features 7 low output impedance drivers that minimize on-chip power dissipation and an actual low power upgrade version for popular ULN2003A family in real applications. When driving a typical 12V relay coil, a ULN2003V12 will dissipate 12 times lower power compared to ULN2003A. ULN2003F12 is a lower power variant benefiting from fewer channel integration and a better fit for applications requiring only 4-channel drivers, such as driving low voltage stepping motors, etc.


The ULN2003V12 and ULN2003F12 both support 3.3V to 5V CMOS logic input interface, thus making it compatible to a wide range of micro-controllers and other logic interfaces, and also feature an improved input interface that minimizes the input DC current drawn from the external drivers. The input RC snubber circuit integrated at ULN2003V12 and ULN2003F12 improves the performance in noisy operating conditions, and the internal pull-down resistor at input stage helps allow input logic to be tri-stated.

As shown in the Functional Diagram, each output of the ULN2003V12 and ULN2003F12 features an internal free-wheeling diode connected in a common-cathode configuration at the COM pin which provides flexibility of increasing current sink capability through combining several adjacent channels in parallel. Under typical conditions the ULN2003V12 can support up to 1.0A of load current when all 7-channels are connected in parallel.

#### **Features**


- 4- and 7-Channel High Current Sink Drivers
- Supports up to 20V Output Pull-up Voltage
- Low Output VOL of 0.6V (Typical) with
  - 100mA (Typ.) Current Sink per Channel at 3.3V Logic Input
  - 140mA (Typ.) Current Sink per Channel at 5.0V Logic Input
- Compatible to 3.3V and 5.0V Micro-Controllers and Logic
- Internal Free-Wheeling Diodes for Inductive Kick-back Protection
- Input Pull-down Resistors Allows Tri-Stating the Input Driver
- Input RC-Snubber to Eliminate Spurious Operation in Noisy Environments
- ESD: 4kV HBM, 1kV CDM
- Available in 16-Pin SOIC, 16-Pin TSSOP and 10-Pin DFN3030 packages
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

## **Pin Assignments**



## SO-16/TSSOP-16

(Top View)



#### U-DFN3030-10

## **Applications**


- Inputs Compatible with Popular Logic Types
- Relay Driver Applications
- Stepping Motor Applications
- Logic Level Shifter


Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Load free
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



# Functional Diagram






ULN2003F12

# **Pin Descriptions**

Pin Name		Package Number		Description
Fill Name	SO16	TSSOP16	DFN3030-10	Description
IN1 ~ IN7	1~7	1~7	1~4	Logic Input Pins IN1 through IN7
GND	8	8	5	Ground Reference Pin
COM	9	9	6	Internal Free-Wheeling Diode Common Cathode Pin
OUT7 ~ OUT1	10~16	10~16	7~10	Channel Output Pins OUT7 through OUT1

# **Functional Block Diagram (Single Channel)**





## Absolute Maximum Ratings (@ TA = +25°C, unless otherwise specified.)

Cumbal	Parameter -		Ra	Rating	
Symbol			Min	Max	Unit
V <sub>IN</sub>	Pin2 IN1~IN7 to GND Voltage		-0.3	5.5	V
V <sub>OUT</sub>	Pins OUT1~OUT7 to GND Voltage		_	20	V
V <sub>COM</sub>	Pin COM to GND Voltage		_	20	V
	Max GND-Pin Continuous Current (+100°C <tj +12<="" <="" td=""><td>5°C)</td><td>_</td><td>700</td><td>mA</td></tj>	5°C)	_	700	mA
I <sub>GND</sub>	Max GND-Pin Continuous Current (T <sub>J</sub> < +100°C)			1.0	А
		16 Pin – SOIC	0.4	412	W
$P_{D}$	Total Device Power Dissipation at T <sub>A</sub> = +85°C	16 Pin – TSSOP	0.277		W
		10 Pin – DFN3030	0.	615	W
	Thermal Resistance Junction-to-Ambient (Note 6)	16 Pin – SOIC	9	97	
$\theta_{JA}$		16 Pin – TSSOP	144		°C/W
		10 Pin – DFN3030	65		
		16 Pin – SOIC	Z	1	
$\theta_{JC}$	Thermal Resistance Junction-to-Case (Note 7)	16 Pin – TSSOP	61		°C/W
		10 Pin – DFN3030			
ESD	НВМ			4	kV
230	CDM			1	kV
$T_J$	Junction Temperature		-55	150	°C
$T_{STG}$	Storage Temperature		-55	150	°C

## Recommended Operating Conditions (@ TA = +25°C, unless otherwise specified.)

Symbol	Parameter		Min	Max	Unit
V <sub>OUT</sub>	Channel Off-Stage Output Pull-Up Voltage		_	_	V
V <sub>COM</sub>	COM Pin Voltage		_	_	V
		VINx = 3.3V	_	1	
IOUT(ON)	Per Channel Continuous Sink Current		_		mA
TJ	Operating Junction Temperature		-40	_	°C

<sup>4.</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only. Functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

5. All voltage values are with respect to the emitter/substrate terminal E, unless otherwise noted.

6. Maximum power dissipation is a function of TJ(max), 0JA, and TA. The maximum allowable power dissipation at any allowable ambient temperature is PD = (TJ(max) = TA)/0 JA. Operating at the absolute maximum TJ of 1450°C can offert a liability.

PD =  $(TJ(max) - TA)/\theta JA$ . Operating at the absolute maximum TJ of +150°C can affect reliability.

<sup>7.</sup> Maximum power dissipation is a function of TJ(max), θJC, and TA. The maximum allowable power dissipation at any allowable ambient temperature is PD = (TJ(max) – TC)/θJA. Operating at the absolute maximum TJ of +150°C can affect reliability.



# Electrical Characteristics (@ T<sub>A</sub> = +25°C, unless otherwise specified.)


Specified over the recommended junction temperature range  $T_J = -40^{\circ}C$  to  $+125^{\circ}C$  and over recommended operating conditions unless otherwise noted. Typical values are at  $T_J = +25^{\circ}C$ .

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
INPUTS IN1 THROUGH IN7 PARAMETERS						
V <sub>I(on)</sub>	IN1~IN7 logic high input voltage	$V_{CE} = 2V, I_{C} = 300mA$	1.65	_	_	V
$V_{I(off)}$	IN1~IN7 logic low input voltage	$I_1 = 250\mu A, I_C = 100mA$	_	1	0.6	V
I <sub>I(on)</sub>	IN1~IN7 ON state input current	I <sub>F</sub> = 350mA		12	25	μA
I <sub>I(off)</sub>	IN1~IN7 OFF state input leakage	_		<b>—</b> )	250	nA
OUTPUTS O	JT1 THROUGH OUT7 PARAMETERS					
		$V_{INX} = 3.3V$ , $I_{OUTX} = 20mA$		0.12	0.15	
V	OUT1 OUT7 love loved output voltage	V <sub>INX</sub> = 3.3V, I <sub>OUTX</sub> = 100mA	1-1	0.6	0.75	V
V <sub>OL(vce-sat)</sub>	OUT1~OUT7 low-level output voltage	$V_{INX} = 5.0V$ , $I_{OUTX} = 20mA$		0.09	0.11	v
		$V_{INX} = 5.0V, I_{OUTX} = 140mA$	7	0.6	0.75	
	OUT1~OUT7 ON-state continuous current at	V <sub>INX</sub> = 3.3V, V <sub>OUTX</sub> = 0.6V	80	100	<u> </u>	V
I <sub>OUT(on)</sub>	$V_{OUTX} = 0.6V$	$V_{INX} = 5.0V, V_{OUTX} = 0.6V$	80	140	_	Α
IOUT(on)	OUT1~OUT7 OFF-state leakage current	$V_{INX} = 0V$ , $V_{OUTX} = V_{COM} = 16V$	. —	0.5	_	μA
SWITCHING	PARAMETERS					
t <sub>PHL</sub>	OUT1~OUT7 logic high propagation delay	$V_{INX} = 3.3V$ , $V_{pull-up} = 12V$ , $R_{pull-up} = 1k\Omega$	_	50	70	ns
t <sub>PLH</sub>	OUT1~OUT7 logic low propagation delay	$V_{INX} = 3.3V$ , $V_{pull-up} = 12V$ , $R_{pull-up} = 1k\Omega$	7	121	140	ns
t <sub>CHANNEL</sub>	Channel-to-channel delay	Over recommended operating conditions and with same test conditions on channels.	_	15	50	ns
R <sub>PD</sub>	IN1~IN7 input pull-down resistance		210k	300k	390k	Ω
ζ	IN1~IN7 input filter time constant		_	9	_	ns
C <sub>OUT</sub>	OUT1~OUT7 output capacitance	$V_{INX} = 3.3V, V_{OUTX} = 0.4V$	_	15	_	pF
FREE-WHEE	LING DIODE PARAMETERS					
VF	Forward voltage drop	$I_{F-peak} = 140mA$ , $VF = V_{OUTx} - V_{COM}$		1.2		V
I <sub>F-peak</sub>	Diode peak forward current		_	140	_	mA




## **Performance Characteristics**


Output Current vs. Input Voltage (One Darlington)




Output Current vs. Output Voltage



Output Current vs. Input Voltage (All Darlingtons in Parallel)




Output Current vs. Output Voltage






## **Performance Characteristics** (continued)


### Output Current vs. Output Voltage



### Diode Forward Voltage vs. Diode Forward Current




## Diode Reverse Current vs. Diode Reverse Voltage





## **Ordering Information**




T16: TSSOP-16 F12: 4 Channels FN: U-DFN3030-10

Device	Dookogo Codo	Dooksaina (Note 0)	7"/13" Tape and Reel		
Device	Package Code	Packaging (Note 8)	Quantity	Part Number Suffix	
ULN2003V12S16-13	S16	SO-16	2,500/Tape & Reel	-13	
ULN2003V12T16-13	T16	TSSOP-16	2,500/Tape & Reel	-13	
ULN2003F12FN-7	FN	DFN3030-10	3,000/Tape & Reel	-7	

8. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging Note:

# **Marking Information**

#### (1) SO-16 and TSSOP-16



YY: Year: 08, 09,10~ WW: Week: 01~52; 52 represents 52 and 53 week

XX: Internal Code

(2) DFN3030-10



XX: Identification Code

<u>Y</u>: Year : 0∼9 <u>W</u>: Week : A∼Z : 1∼26 week;

a~z: 27~52 week; z represents

52 and 53 week X: Internal Code


Part Number	Package	Identification Code
ULN2003F12FN-7	DFN3030-10	A3




# **Package Outline Dimensions**

Please see http://www.diodes.com/package-outlines.html for the latest version.

### **SO-16**



SO-16					
Dim	Min	Max	Тур		
Α	-	1.260			
A1	0.10	0.23			
A2	1.02				
b	0.31	0.51			
С	0.10	0.25			
D	9.80	10.00			
Е	5.90	6.10			
E1	3.80	4.00			
е	1.27 BSC				
h	0.15	0.25	0.20		
L	0.40	1.27			
L1	1.04 REF				
L2	(	).25 BS(	)		
R	0.07				
R1	0.07				
Χ	3.945 REF				
Υ		.661 RE	F		
θ	0°	8°			
θ1	5°	15°			
θ2	0°				
All	Dimens	ions in	mm		




TSSOP-16					
Dim	Min	Max	Тур		
Α	-	1.08	-		
A1	0.05	0.15	-		
A2	0.80	0.93	-		
b	0.19	0.30	-		
С	0.09	0.20	-		
D	4.90	5.10	-		
Е	6.40 BSC				
E1	4.30	4.50	-		
е	(	).65 BS	С		
L	0.45	0.75	-		
L1	1	.00 RE	F		
L2	(	).25 BS	С		
R / R1	0.09	-	-		
Х	-	-	1.350		
Υ	-	-	1.050		
θ	0°	8°	-		
θ1	5°	15°	-		
θ2	0°	-	-		
All Dimensions in mm					



## Package Outline Dimensions (continued)

Please see http://www.diodes.com/package-outlines.html for the latest version.

# U-DFN3030-10




U-DFN3030-10					
Dim	Min	Max	Тур		
Α	0.57	0.63	0.60		
A1	0.00	0.05	0.02		
А3	_	_	0.15		
b	0.20	0.30	0.25		
D	2.90	3.10	3.00		
D2	2.30	2.50	2.40		
ш	2.90	3.10	3.00		
E2	1.50	1.70	1.60		
е	-		0.50		
Г	0.25	0.55	0.40		
z			0.375		
All Dimensions in mm					

# **Suggested Pad Layout**

Please see http://www.diodes.com/package-outlines.html for the latest version.






Dimensions	Value (in mm)
С	1.270
X	0.670
X1	9.560
Y	1.450
Y1	6.400



## Suggested Pad Layout (continued)


Please see http://www.diodes.com/package-outlines.html for the latest version.

#### TSSOP-16



Dimensions	Value (in mm)
С	0.650
Х	0.350
X1	4.900
Y	1.400
Y1	6.800

## U-DFN3030-10



Dimensions	Value			
Dimensions	(in mm)			
С	0.50			
G	0.15			
Х	0.35			
X1	2.60			
Υ	0.60			
V1	1.80			

## **Mechanical Data**

- Moisture Sensitivity: Level 3 per J-STD-020
- Terminals:
  - SO-16 and TSSOP-16: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 (3)
  - **DFN3030-10**: Finish NiPdAu over Copper Lead-Frame, Solderable per MIL-STD-202, Method 208 <sup>®</sup>3
- Weight:
  - SO-16: 0.129 grams (Approximate)
  - TSSOP-16: 0.055 grams (Approximate)
  - **DFN3030-10**: 0.016 grams (Approximate)



#### IMPORTANT NOTICE

- 1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<a href="https://www.diodes.com/about/company/terms-and-conditions-of-sales/">https://www.diodes.com/about/company/terms-and-conditions-of-sales/</a>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.
- 9. This Notice may be periodically updated with the most recent version available at <a href="https://www.diodes.com/about/company/terms-and-conditions/important-notice">https://www.diodes.com/about/company/terms-and-conditions/important-notice</a>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries. All other trademarks are the property of their respective owners.

© 2024 Diodes Incorporated. All Rights Reserved.

www.diodes.com