



UL Flammability Classification Rating 94V-0

### 465V NPN HIGH VOLTAGE POWER TRANSISTOR

Case Material: Molded Plastic, "Green" Molding Compound;


### **Features**

- BV<sub>CEO</sub> > 465V
- **BV<sub>CES</sub> > 700V**
- BV<sub>FBO</sub> > 9V
- I<sub>C</sub> = 1.5A high Continuous Collector Current
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

## **Applications**


Low power AC-DC SMPS for:

- Battery Chargers for Mobile Phone / Tablets / Smartphones
- Power Supply for DVD / STB
- LED lighting



**Mechanical Data** 

Case: TO126



# Ordering Information (Note 4)

Product	Package	Marking	Quantity
APT13003EU-G1	TO126	GU13003E	4000 Bulk, Loose per Box


Notes:

EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. All applicable RoHS exemptions applied.

В

- 2. See http://www.diodes.com/quality/lead\_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.</p>
  4. For packaging details, go to our website at http://www.diodes.com/products/packages.html.

## **Marking Information**



= Manufacturers' Code Marking GU13003E = Product Type Marking ID YWW = Date Code Marking e.g. 312 = Year 2013, Week 12. 8 = Assembly site code XX = Batch Number

Front Face View

1 of 6 www.diodes.com



## Absolute Maximum Ratings (@T<sub>A</sub> = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Emitter Voltage (V <sub>BE</sub> = 0V)	$V_{CES}$	700	V
Collector-Emitter Voltage	$V_{CEO}$	465	V
Emitter-Base Voltage	$V_{EBO}$	9	V
Continuous Collector Current	I <sub>C</sub>	1.5	Α
Peak Pulse Collector Current(Note 5)	Ісм	3	Α
Continuous Base Current	lΒ	0.75	Α
Peak Pulse Base Current(Note 5)	I <sub>BM</sub>	1.5	Α

Note:

5. Pulse test for pulse width < 5ms, duty cycle ≤ 10%.

## Thermal Characteristics (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation	$P_D$	20	W
Thermal Resistance, Junction to Ambient Air	R <sub>0</sub> JA	96	°C/W
Thermal Resistance, Junction to Case	R <sub>0</sub> JC	6.25	°C/W
Operating and Storage Temperature Range	$T_{J,}T_{STG}$	-65 to +150	°C


## ESD Ratings (Note 6)

Characteristic	Symbol	Value	Unit	JEDEC Class
Electrostatic Discharge - Human Body Model	ESD HBM	≥ 8,000	V	3B
Electrostatic Discharge - Machine Model	ESD MM	≥ 400	V	С

Note:

6. Refer to JEDEC specification JESD22-A114 and JESD22-A115.

# Safe Operating Area (@T<sub>A</sub> = +25°C, unless otherwise specified.)



Safe Operating Areas (TO-126 Package)



## Electrical Characteristics (@T<sub>A</sub> = +25°C, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Collector-Emitter Breakdown Voltage	BV <sub>CES</sub>	700	_	_	V	I <sub>C</sub> = 100μA, V <sub>BE</sub> = 0V
Collector-Emitter Breakdown Voltage	BV <sub>CEO</sub>	465	_	_	V	I <sub>C</sub> = 100μA
Emitter-Base Breakdown Voltage	BV <sub>EBO</sub>	9	_	_	V	I <sub>E</sub> = 100μA
Collector Cutoff Current	I <sub>CEV</sub>	_	_	10	μA	V <sub>CE</sub> = 700V, V <sub>BE</sub> = -1.5V
DC current transfer Static ratio (Note 7)	h <sub>FE</sub>	15 13 5	_ 17 _	— 30 25		$I_C = 0.3A$ , $V_{CE} = 2V$ $I_C = 0.5A$ , $V_{CE} = 2V$ $I_C = 1.0A$ , $V_{CE} = 2V$
Collector-Emitter Saturation Voltage (Note 7)	V <sub>CE(sat)</sub>	_ _	0.17 0.29	0.3 0.4	l V	$I_C = 0.5A$ , $I_B = 0.1A$ $I_C = 1A$ , $I_B = 0.25A$
Base-Emitter Saturation Voltage (Note 7)	V <sub>BE(sat)</sub>	_		1.0 1.2	V	$I_C = 0.5A$ , $I_B = 0.1A$ $I_C = 1A$ , $I_B = 0.25A$
Output Capacitance	C <sub>ob</sub>	_	16	-	pF	V <sub>CB</sub> = 10V, f = 0.1MHz
Transition Frequency	f <sub>T</sub>	4	_	-	MHz	I <sub>C</sub> = 0.1A, V <sub>CE</sub> = 10V
Turn-on Time with Resistive Load	ton	_	0.3	1		
Storage Time with Resistive Load	ts	_	1.8	3	μs	$I_C = 1A, V_{CC} = 125V, I_{B1} = 0.2A,$ $I_{B2} = -0.2A, t_0 = 25\mu s$
Fall Time with Resistive Load	t <sub>f</sub>	_	0.28	0.4		1820.2M, ip - 25µs

Note: 7. Measured under pulsed conditions. Pulse width ≤ 300µs. Duty cycle ≤ 2%.







## Typical Electrical Characteristics (@TA = +25°C, unless otherwise specified.)




Static Characteristics




Collector-emitter Saturation Voltage



h<sub>FE</sub> vs. Case Temperature



DC Current Gain vs. Collector Current




Base-emitter Saturation Voltage



## **Package Outline Dimensions**

 $Please see \ http://www.diodes.com/package-outlines.html \ for \ the \ latest \ version.$ 

### TO126



TO126						
Dim	Min	Max	Тур			
Α	2.400	2.900				
A2	1.060	1.500				
b	0.660	0.860	-			
b1	1.170	1.470	-			
С	0.400	0.600	-			
D	7.400	8.200	<b>-</b>			
Е	10.60	11.20				
е	-	1	2.280			
e1	-	-	4.560			
h	0.00	0.30	-			
٦	14.50	15.90	-			
L1	1.700	2.100	-			
Υ	3.600	3.900	-			
Ø	3.100	3.550	-			
All Dimensions in mm						

Note: For high voltage applications, the appropriate industry sector guidelines should be considered with regards to voltage spacing between terminals.





#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com

